



ITEM	Q'TY	PART NUMBER	PART DESCRIPTION
1	1	FLP-LC	HOLDER CAP, FLEXIBLE LIGHT-PIPE
2	1	FLPS1022-X.XXX	LIGHT PIPE CABLE, CUT LENGTH IN INCHES

REV.	DESCRIPTION	DATE	APPROVED
H	FLP Length Update	10/18/05	M. C.
J	FLP Length Clarification	01/11/06	M. C.
K	Corrected "L" Dimension Measurement	07/25/07	M. C.
M	Updated Fiber In BOM	11/14/12	T. Y.
N	Added Note 2	10/06/16	J. C.




" L "	Tolerance
0.750" ~ 16.000"	±0.050"
16.100" ~ 40.000"	±0.150"
40.100" ~ 80.000"	±0.300"
80.100" ~ 3,940.0"	±0.5%

NOTE:

1. ALLOWABLE CUT LENGTH IS UP TO 3 DECIMAL PLACES.

2. MINIMUM BEND RADIUS OF FLEXIBLE LIGHT PIPE: 0.87" [22mm].

STANDARD TOLERANCE (UNLESS OTHERWISE SPECIFIED)		<div>BIVAR[®]</div> <div>4 THOMAS, IRVINE, CA. 92618</div> <div>TEL: (949) 951-8808 FAX: (949) 951-3974</div>	
<u>DECIMALS</u>	<u>ANGULAR</u>		
.X ± .1	X° ± 1°	<div></div> <div>TITLE: LENS CAP / FLP ASSEMBLY, 4mm ROUND</div>	
.XX ± .02			
.XXX ± .010			
DESIGNED: S. Irving	DATE: 05/22/02	PART NO: LC-XX.X	REVISION: N
CHECKED: M. Chen	DATE: 05/22/02	CAGE CODE : 32559	SHEET # 1 OF 1
CAD GENERATED DOCUMENT. DO NOT MEASURE DRAWING.			