

Threaded Adapters

NPT Threaded Adapters

User assumes all responsibility for using adapters safely

| | Part Number | Exposed Threads | Length | Wrench Flats |
|---|-------------|---------------------------------|----------------|--------------|
|  95713 | 95713 | 1/4" NPT Female – 1/8" NPT Male | 25 mm (1") | – |
|  95714 | 95714 | 3/8" NPT Female – 1/4" NPT Male | 32 mm (1-1/4") | – |
|  95394 | 95394 | 1/2" NPT Female – 3/8" NPT Male | 44 mm (1-3/4") | – |

Collet-to-Thread Adapters

User assumes all responsibility for using adapters safely

| | Part Number | Exposed Threads | Shank Dia. | Length | Wrench Flats |
|---|-------------|-----------------------------|------------|----------------|--------------|
|  50103 | 50103 | 1/4" Shank – 1/4"-20 Male | 1/4" | 32 mm (1-1/4") | 11 mm |
|  51032 | 51032 | 1/4" Shank – 1/4"-20 Female | 1/4" | 38 mm (1-1/2") | – |

Threaded Adapters

User assumes all responsibility for using adapters safely

| | Part Number | Exposed Threads | Length | Wrench Flats |
|---|-------------|----------------------------------|-----------------|--------------|
|  04117 | 04117 | M x 8 Female – 3/8"-24 Male | 19 mm (3/4") | 12 mm |
|  18908 | 18908 | M x 8 Female – 3/8"-24 Male | 35 mm (1-3/8") | 11 mm |
|  54021 | 54021 | 1/4"-28 Male – 1/4"-20 Male | 30 mm (1-3/16") | 14 mm |
|  53181 | 53181 | 3/8"-24 Male – 1/2"-20 Male | 25 mm (1") | 19 mm |
|  50149 | 50149 | 3/8"-24 Female – M14 x 2 Male | 25 mm (1") | 19 mm |
|  50106 | 50106 | 3/8"-24 Female – 1/4"-20 Male | 27 mm (1-1/16") | 14 mm |
|  42636 | 42636 | 3/8"-24 Female – 3/8"-24 Male | 25 mm (1") | 9 mm |
|  93696 | 93696 | 3/8"-24 Female – 3/8"-24 Male | 25 mm (1") | 17 mm |
|  97103 | 97103 | 3/8"-24 Female – 1/2"-20 Male | 51 mm (2") | 16 mm |
|  53549 | 53549 | 3/8"-24 Female – 1/2"-20 Male | 51 mm (2") | 16 mm |
|  55064 | 55064 | 3/8"-24 Female – 5/8"-11 Male | 25 mm (1") | 17 mm |
|  55034 | 55034 | 3/8"-24 Female – 5/8"-11 Male | 35 mm (1-3/8") | 17 mm |
|  53652 | 53652 | 3/8"-24 Female – 5/8"-11 Male | 38 mm (1-1/2") | 24 mm |
|  98050 | 98050 | 3/8"-24 Female – 5/8"-11 Male | 51 mm (2") | 3/4" |
|  98085 | 98085 | 3/8"-24 Female – 5/8"-11 Male | 64 mm (2-1/2") | 3/4" |
|  51029 | 51029 | 3/8"-24 Female – 1/4"-20 Female | 38 mm (1-1/2") | 16 mm |
|  54039 | 54039 | 3/8"-24 Female – 5/16"-24 Female | 25 mm (1") | 17 mm |
|  14081 | 14081 | 1/2"-20 Female – 5/8"-11 Male | 44 mm (1-3/4") | 19 mm |
|  54040 | 54040 | 5/8"-11 Female – 5/16"-24 Female | 41 mm (1-5/8") | 19 mm |
|  58058 | 58058 | 5/8"-11 Female – 5/8"-11 Male | 51 mm (2") | 19 mm |
|  13060 | 13060 | 5/8"-11 Female – 5/8"-11 Male | 102 mm (4") | 19 mm |