

# Electric Dynafile® II

- Grind, sand and deburr in those tight areas.
- Reversible side handle. Grinding head pivots 360°.

## 120 V (AC), 6-amp

Includes contact arm for 1/2" W x 18" L abrasive belts.

**11,000 RPM**

**Model 40610**



Kit includes 40610 tool,  
2 additional contact arms,  
assortment of platen pads  
& abrasives and carry case.



**Versatility Kit**

**Model 40611**

# Electric Grinder

- 11,000 RPM; 120 V (AC), 6-amp. 5/8"-11 spindle thread.
- Accepts optional wheels/flap discs with 7/8" center hole.

## Electric Depressed Center Wheel Grinder

Shown with optional  
Type 27 Depressed  
Center Wheel.



**4-1/2" Diameter**

**Model 40260**

