

Non-Vacuum Random Orbital Sanding Pads

- Premium urethane, weight-mated to Dynabrade tools.
- Dynabrade's exclusive single-piece hub design!
- 13,000 RPM maximum, 5/16"-24 male thread.

Non-Vacuum

PSA

Ideal for PSA-Type disc adhesion.



Diameter	Part No.	Thickness	Density
3"	56084	5/8"	Medium
	56086	5/8"	Soft
3-1/2"	56097	5/8"	Soft
	56098	5/8"	Medium
5"	56102	3/8"	Soft
	56106	3/8"	Medium
	56175	5/8"	Medium
	56185	5/8"	Soft
	56273	1/2"	Extra Soft
6"	56103	3/8"	Soft
	56107	3/8"	Medium
	56177	5/8"	Medium
	56187	5/8"	Soft
8"	56234	3/8"	Medium

Non-Vacuum

Hook-Face

Short nap for reattachable discs.

Long nap for non-woven nylon discs.



Diameter	Part No.	Thickness	Nap	Density
3"	56087	5/8"	Short	Medium
	56090	5/8"	Long	Medium
	56145	1/2"	Short	Medium
3-1/2"	54311	5/8"	Short	Soft
	54313	5/8"	Short	Hard
	54314	5/8"	Long	Medium
5"	54325	3/8"	Short	Medium
	56157	3/8"	Short	Soft
	56180	5/8"	Short	Medium
	56195	5/8"	Short	Soft
6"	54327	3/8"	Short	Medium
	56158	3/8"	Short	Soft
	56182	5/8"	Short	Medium
	56197	5/8"	Short	Soft
8"	56236	3/8"	Short	Medium