

# Vacuum Random Orbital Sanding Pads

- Premium urethane, weight-mated to Dynabrade tools.
- Dynabrade's exclusive single-piece hub design!
- 13,000 RPM maximum, 5/16"-24 male thread.

## Vacuum

### PSA

Ideal for PSA-Type disc adhesion.



Diameter	Part No.	Holes	Thickness	Density
3"	56084	0	5/8"	Medium
	56086	0	5/8"	Soft
3-1/2"	56097	0	5/8"	Soft
	56098	0	5/8"	Medium
5"	56100	5	3/8"	Soft
	56104	5	3/8"	Medium
	56176	5	5/8"	Medium
	56186	5	5/8"	Soft
	56241	6	3/8"	Medium
	56274	5	1/2"	Extra Soft
6"	56101	6	3/8"	Soft
	56105	6	3/8"	Medium
	56178	6	5/8"	Medium
	56188	6	5/8"	Soft
8"	56235	5	3/8"	Medium

## Vacuum

### Hook-Face

Short nap for reattachable discs.

Long nap for non-woven nylon discs.



Diameter	Part No.	Holes	Thickness	Density
3"	56087	0	5/8"	Medium
	56090	0	5/8"	Medium
	56142	6	1/2"	Medium
3-1/2"	54311	0	5/8"	Soft
	54313	0	5/8"	Medium
	54314	0	5/8"	Medium
5"	54326	5	3/8"	Medium
	56155	5	3/8"	Soft
	56181	5	5/8"	Medium
	56196	5	5/8"	Soft
	56240	6	3/8"	Medium
	56320	44	3/8"	Medium
6"	54328	6	3/8"	Medium
	56156	6	3/8"	Soft
	56183	6	5/8"	Medium
	56198	6	5/8"	Soft
	56321	52	3/8"	Medium
8"	56322	48	3/8"	Medium

**\*NOTE:** Pads without holes can be used for vacuum sanding. Vacuum pick-up is around periphery of pad.