

DynaBrite Belts

NON-WOVEN NYLON ABRASIVES



Common Applications

DynaBrite belts are made of a non-woven nylon which is impregnated with abrasive grain and resin, perfect for:

- Light and heavy duty cleaning
- Deburring
- Blending
- Polishing
- Finishing



☑ Please call for availability

Length	Width	Brand	SE Coarse Brown	Coarse Brown	Medium Maroon	Very Fine Blue	Super Fine Grey	Polishing White
7-3/8 (187 mm)	3" (76 mm)	DYNABRADE	☑	☑	90092	90091	90090	☑
9-3/4" (248 mm)	2-1/4" (57 mm)	DYNABRADE	☑	☑	90095	90094	90093	☑
10-11/16" (271 mm)	3" (76 mm)	DYNABRADE	☑	90239	90238	90237	90219	☑
		3M	☑	89213	89212	89211	89210	90048
	7" (178 mm)	DYNABRADE	☑	☑	90098	90097	90096	☑
12" (305 mm)	1/2" (13 mm)	DYNABRADE	78005	78006	78007	78008	78009	☑
		3M	90315	90314	90313	90312	90311	☑
15-1/2" (394 mm)	2-3/4" (70 mm)	DYNABRADE	☑	90023	90022	90021	90013	☑
		3M	☑	89233	89232	89231	☑	☑
	3-1/2" (89 mm)	DYNABRADE	☑	90283	90282	90281	90014	☑
		3M	89244	89243	89242	89241	89240	90051



For **surface conditioning**, not material removal

Dynabrade Rubber Drive Wheel

For best results, make use of our rubber drive wheels. Ideal for use with DynaBrite surface conditioning belts.