

Network of Authorized Distributors

We have been supplying high quality tools to customers through a worldwide network of professional distributors who are capable of meeting the specific needs of the industrial and automotive aftermarkets. Our distributors have extensive knowledge of Dynabrade's complete line of power tools and related accessories. Their goal is to improve customer's competitiveness by minimizing costs through a continuous improvement process.

FREE Demonstration Policy

We can arrange a no-obligation demonstration in your facility on most of our products. It is a sure way to see that the product is best suited to your application and to see the time, labor and cost-saving advantages of Dynabrade products. Contact your local Dynabrade distributor to arrange an in-plant demonstration. To contact your local Dynabrade distributor, call our Customer Service Department, or visit our distributor locator on our website.

Lifetime Warranty on Pneumatic Tools

All Dynabrade portable pneumatic power tools are rigorously inspected and performance-tested in our factory before shipping to our customers. If a Dynabrade tool develops a performance problem and an inherent defect is found during normal use and service, Dynabrade will warrant this tool against defects in workmanship and materials for the lifetime of the tool. Contact our Customer Service Department for details.

Customer Service

1-800-828-7333

Dynabrade's customer service staff has just one very important job – to make sure that you are completely satisfied with your order and service. Our Customer Service Department is staffed with highly trained individuals, ready to serve you in any way they can, from order-taking to technical service to rush shipments! To more efficiently serve the international marketplace, our Luxembourg office can communicate in fourteen languages. In short, our commitment to customer service is to satisfy our customers by serving them well. If we can help or improve in any way, we'd like to hear from you.



DYNORBITAL® SILVER SUPREME SANDER

- Supreme Power with Lightweight Comfort!
- The Most DURABLE Sander on The Market Today
- Includes Premium Weight-Mated Sanding Pad

12,000 RPM Non-Vacuum

- Conversion kits available to easily convert Non-Vac to a vacuum tool.

Pad Diameter	3/8" Orbit Models	3/16" Orbit Models	3/32" Orbit Models
3"	69100	69105	69110
3-1/2"	69000	69015	69030
5"	69005	69020	69035
6"	69010	69025	69040



12,000 RPM Self-Generated Vac

- Ready for connection to optional portable self-contained dust collection systems.

Pad Diameter	3/8" Orbit Models	3/16" Orbit Models	3/32" Orbit Models
3"	69103	69108	69113
3-1/2"	69003	69018	69033
5"	69008	69023	69038
6"	69013	69028	69043



12,000 RPM Central Vacuum

- Has 1" outside dia. vacuum port for easy connection to central vacuum systems.

Pad Diameter	3/8" Orbit Models	3/16" Orbit Models	3/32" Orbit Models
3"	69104	69109	69114
3-1/2"	69004	69019	69034
5"	69009	69024	69039
6"	69014	69029	69044

