

2" DIA. DISC SANDERS

RIGHT ANGLE .33 HP

18,000 RPM

Model 52590

- Includes 51345 Locking-Type Pad; rear exhaust, standard muffler.



ANGLE HEAD .4 HP

3,200 RPM

Model 53410

- Tool has 1/4"-28 female thread; includes 54021 Adapter for pads with 1/4"-20 female thread and 50107 Pad for PSA abrasive discs.



7° OFFSET, .4 HP

- Rear exhaust, gearless; includes 51344 Locking-Type Pad.

25,000 RPM

Model 52500

- Extended muffler.

Model 52503

- Standard muffler.



RIGHT ANGLE, .4 HP

- Includes 51344 Locking-Type Pad.



Model No.	Motor RPM	Exhaust	Muffler Type
51820	12,000	Front	—
51821	15,000	Front	—
51822	20,000	Front	—
52520	12,000	Rear	Extended
52521	15,000	Rear	Extended
52522	20,000	Rear	Extended
52540	12,000	Rear	Standard
52541	15,000	Rear	Standard
52542	20,000	Rear	Standard

7° OFFSET, .5 HP

- Includes 51344 Locking-Type Pad.

15,000 RPM

Model 52400

- Front exhaust.

20,000 RPM

Model 52402

- Front exhaust.



Model 52405

- Rear exhaust, extended muffler.