

High-holding Acrylic Adhesive 350 - 5.0 mil

3M™ Adhesive Transfer Tape 9485PC

- Polycoated Kraft (PCK) 58#
- 5.0 mil, 350 high holding acrylic adhesive
- 4.0 mil, 58 lb poly-coated kraft paper liner
- High tack, shear and temperature performance
- High solvent resistance
- HSE and LSE
- Good adhesion to LSE plastics and foams

UPC Code	Model	Size	Thickness	Quantity
0 00 21200 63462 8	9485PC	24 in x 60 yd	5.0 mil	1/case
0 00 21200 63476 5	9485PC	1/2 in x 60 yd	5.0 mil	72/case
0 00 21200 63477 2	9485PC	1 in x 60 yd	5.0 mil	36/case
0 00 21200 67233 0	9485PC	3/4 in x 60 yd	5.0 mil	48/case
0 00 21200 67413 6	9485PC	2 in x 60 yd	5.0 mil	24/case
0 00 21200 84254 2	9485PC	10 in x 60 yd	5.0 mil	4/case
0 00 21200 37911 6	9485PC	48 in x 60 yd	5.0 mil	1/case
0 00 21200 37910 9	9485PC	48 in x 180 yd	5.0 mil	1/case
0 00 21200 39609 0	9485PC	3 in x 60 yd	5.0 mil	12/case
0 00 21200 39611 3	9485PC	12 in x 60 yd	5.0 mil	4/case
0 00 21200 40782 6	9485PC	1-1/2 in x 60 yd	5.0 mil	24/case
0 00 21200 40783 3	9485PC	36 in x 60 yd	5.0 mil	1/case
0 00 21200 40784 0	9485PC	3/8 in x 60 yd	5.0 mil	96/case
0 00 21200 40785 7	9485PC	4 in x 60 yd	5.0 mil	8/case
0 00 21200 40786 4	9485PC	6 in x 60 yd	5.0 mil	8/case
0 00 21200 43107 4	9485PC	1-1/4 in x 60 yd	5.0 mil	24/case

High Performance Acrylic Adhesive 200MP - 2.0 mil

3M™ Adhesive Transfer Tape 467MP

- Polycoated Kraft (PCK) 58#
- High temperature, acrylic formulation that withstands temperatures up to 400°F
- Excellent shear strength, making it ideal for graphics attachments and die-cut parts
- Resists solvents
- Excellent moisture stability and resistance to solvents
- Liner is moisture resistant

UPC Code	Model	Size	Thickness	Color	Quantity
0 00 21200 19330 9	467MP	1/2 in x 60 yd	2.0 mil	Clear	72/case
0 00 21200 19331 6	467MP	3/4 in x 60 yd	2.0 mil	Clear	48/case
0 00 21200 19332 3	467MP	1 in x 60 yd	2.0 mil	Clear	36/case
0 00 21200 19333 0	467MP	2 in x 60 yd	2.0 mil	Clear	24/case
0 00 21200 19334 7	467MP	3 in x 60 yd	2.0 mil	Clear	12/case
0 00 21200 68158 5	467MP	12 in x 60 yd	2.0 mil	Clear	4/case
0 00 21200 68157 8	467MP	24 in x 60 yd	2.0 mil	Clear	1/case

To convert units of measure or performance, refer to the last page of this section.
The product calipers listed are nominal; please refer to specific product data pages for more detailed information.