


# Random Orbital Sander Accessories

## 3M™ Stikit™ Disc Pads



Part No.	Max RPM	Max OPM	Diameter Inch (mm)	Thread Size	Density Rating	Face Color	UPC	MOQ
<b>Low Profile Disc Pads (Firm)</b>								
20348	15,000	15,000	3 (76)	1/4-20 EXT	Firm	Blue	051141-20348-5	10
20351	12,000	12,000	5 (125)	5/16-24 EXT	Firm	Blue	051141-20351-5	1
20354	12,000	12,000	6 (152)	5/16-24 EXT	Firm	Blue	051141-20354-6	1
<b>Standard Profile Disc Pads (Medium)</b>								
70234	12,000	—	5 (125)	5/8-11 INT	Medium	Blue	051111-55813-3	5
82189	12,000	—	5 (125)	5/8-11 INT	Medium	Red	051144-82189-1	10
05575	10,000	12,000	5 (125)	5/16-24 EXT	Medium	Blue	051144-05575-3	1
28772	10,000	12,000	6 (152)	5/16-24 EXT	Medium	Blue	051141-28772-0	1
<b>Low Profile Finishing Disc Pads (Soft)</b>								
05545	12,000	12,000	5 (125)	5/16-24 EXT	Soft	Blue	051131-05545-2	10
05546	10,000	12,000	6 (152)	5/16-24 EXT	Soft	Blue	051131-05546-9	1

## 3M™ Stikit™ D/F Disc Pads (Vacuum)



Part No.	Max RPM	Max OPM	Diameter Inch (mm)	Thread Size	# of Holes	Density Rating	Face Color	UPC	MOQ
<b>Low Profile Disc Pads (Firm)</b>									
20442	12,000	12,000	5 (125)	5/16-24 EXT	5	Firm	Blue	051141-20442-0	1
20454	12,000	12,000	6 (152)	5/16-24 EXT	6	Firm	Blue	051141-20454-3	1
<b>Standard Profile Disc Pads (Medium)</b>									
45217	10,000	12,000	5 (125)	5/16-24 EXT	5	Medium	Blue	051144-45217-0	10
45218	10,000	12,000	6 (152)	5/16-24 EXT	6	Medium	Blue	051144-45218-7	10
<b>Low Profile Finishing Disc Pads (Soft)</b>									
05645	12,000	12,000	5 (125)	5/16-24 EXT	5	Soft	Blue	051131-05645-9	10
05646	10,000	12,000	6 (152)	5/16-24 EXT	6	Soft	Blue	051131-05646-6	1


# 3M™ Power Tool Accessories — Quick Reference

## 3M™ Filter Bags and Adapters




UPC	Size
<b>3M™ Clean Sanding Filter Bag — HEPA-rated</b>	
051141-20452-9	Large — Holds up to 1/2 lb.
051141-28364-7	Extra Large — Holds up to 3 lbs.
<b>3M™ Clean Sanding Filter Bag Backpack Assembly</b>	
051141-28365-4	—
<b>3M™ Filter Bag Adapter</b>	
051141-20453-6	1" EXT Hose Thread x 1" ID

## 3M™ Hookit™ Clean Sanding Disc Pads



UPC	Size	Thickness	Density
<b>Max RPM/OPM = 12,000</b>			
051141-20428-4	3" x 1/4-20 EXT	3/4"	Soft
051141-20290-7	5" x 5/16-24 EXT	11/16"	Soft
051141-20353-9	5" x 5/16-24 EXT	3/8"	Firm
051141-20465-9	6" x 5/16-24 EXT	3/8"	Firm
051141-20356-0	6" x 5/16-24 EXT	3/8"	Firm
051141-20425-3	6" x 5/16-24 EXT	1/2"	Soft
<b>Max RPM/OPM = 15,000</b>			
051141-20350-8	3" x 1/4-20 EXT	1/2"	Firm

## 3M™ Hookit™ Disc Pads



UPC	Size	Thickness	Density
<b>Max RPM/OPM = 12,000</b>			
051131-05775-3	5" x 5/16-24 EXT	3/4"	Medium
051141-20352-2	5" x 5/16-24 EXT	3/8"	Firm
051144-77855-3	5" x 5/16-24 EXT	11/16"	Soft
051141-20355-3	6" x 5/16-24 EXT	3/8"	Firm
<b>Max RPM/OPM = 15,000</b>			
051141-28472-9	3" x 1/4-20 EXT	1/2"	Firm

## 3M™ Stikit™ Disc Pads



UPC	Diameter	Thickness	Density
<b>Max OPM/RPM = 15,000</b>			
051141-20348-5	3" x 1/4-20 EXT	1/2"	Firm
<b>Max RPM = 12,000</b>			
051111-55813-3	5" x 5/8-11 INT	1/2"	Medium
051144-82189-1	5" x 5/8-11 INT	3/4"	Medium
<b>Max OPM = 12,000 Max RPM = 10,000</b>			
051144-05575-3	5" x 5/16-24 EXT	3/4"	Medium
051131-05546-9	6" x 5/16-24 EXT	11/16"	Soft
<b>Max OPM/RPM = 12,000</b>			
051141-20351-5	5" x 5/16-24 EXT	3/8"	Firm
051131-05545-2	5" x 5/16-24 EXT	11/16"	Soft
051141-20354-6	6" x 5/16-24 EXT	3/8"	Firm

## 3M™ Hookit™ Clean Sanding Pads



UPC	Size	Thickness	Density
<b>Max OPM = 10,000</b>			
051141-20435-2	3" x 4"	1/2"	Medium
051141-28531-3	70mm x 198mm	12.7mm	Medium

## 3M™ Hookit™ Pad



UPC	Size	Thickness	Density	Max OPM
051141-20433-8	3" x 4"	1/2"	Medium	10,000

## 3M™ Finesse-it™ Buffing Pads



UPC	Diameter	Description
<b>Max OPM = 12,000</b>		
051111-51151-0	3-1/4"	Orange Foam/White Loop
051141-20271-6	3-3/4"	White Foam/White Loop
051111-51158-9	3-3/4"	Orange Foam/White Loop
051111-51076-6	5-1/4"	Orange Foam/White Loop
051141-28878-9	3-1/4"	Gray Foam; Waffle Face
051141-28879-6	3-3/4"	Gray Foam; Waffle Face
051141-28880-2	5-1/4"	Gray Foam; Waffle Face
051141-28873-4	3-1/2"	Gray Foam; Flat Face
051125-87391-8	5-1/4"	Gray Foam; Flat Face
051141-28869-7	3-1/4"	Green Foam; Waffle Face
051141-28870-3	3-3/4"	Green Foam; Waffle Face
051141-28871-0	5-1/4"	Green Foam; Waffle Face
051141-28872-7	3-1/2"	Green Foam; Flat Face
051141-28874-1	3-1/4"	Red Foam; Waffle Face
051141-28875-8	3-3/4"	Red Foam; Waffle Face
051141-28876-5	5-1/4"	Red Foam; Waffle Face
051141-28877-2	3-1/2"	Red Foam; Flat Face

## 3M™ Roloc™ Shank



UPC	Shank Size	Thread Size
051144-45102-9	1/4"	1/4-20 EXT

## 3M™ Roloc™ Disc Pads



UPC	Size	Max RPM	Density
<b>Roloc™ TR (Plastic Button)</b>			
051144-45096-1	2" x 1/4-20 INT	25,000	Hard
051144-45091-6	3" x 1/4-20 INT	20,000	Hard
051144-83980-3	4" x 5/8-11 INT	12,000	Extra Hard
051141-28475-0	4" x 3/8-24 INT	12,000	Extra Hard
<b>Roloc™ TS/TSM</b>			
051144-14212-5	2" x 1/4-20 INT	25,000	Hard
051144-14216-3	3" x 1/4-20 INT	20,000	Hard
051144-28577-1	4" x 3/8-24 INT	12,000	Extra Hard
051144-28579-5	4" x 5/8-11 INT	12,000	Extra Hard

## 3M™ Hookit™ Roloc™ Disc Pads

UPC	Diameter	Max OPM	Max RPM
<b>Roloc™ TR (Plastic Button)</b>			
051144-82564-6	1"	10,000	8,000
051111-60311-6	1-1/16"	10,000	10,000
051144-82565-3	1-1/2"	10,000	8,000
051144-82566-0	2"	10,000	8,000
051144-82567-7	3"	10,000	8,000

## 3M™ Finesse-it™ Roloc™ Backup Pad — TR

051111-50198-6	1-1/4"	Medium	12,000
----------------	--------	--------	--------

## 3M™ Disc Pad Hubs



UPC	Diameter	Thread Size
051141-28442-2	2-1/2"	3/8-24 INT x 5/8-11 EXT
051141-28476-7	2-1/2"	5/8-11 INT

## Disc Pad Holders (Hook-and-Loop)



UPC	Size	Max RPM
048011-07494-8	2" x 1/4" shank	23,000
048011-04132-2	3" x 1/4" shank	20,000
048011-07492-4	4" x 1/4" shank	13,000
048011-05674-6	4" x 5/8-11 INT	13,000
048011-14111-4	4-1/2" x 5/8-11 INT	13,000

## 3M™ Disc Pad Face Plates



UPC	Diameter	Hardness	Max RPM
<b>Ribbed</b>			
051141-28656-3	4"	Extra Hard	15,000
051141-28443-9	4-1/2"	Extra Hard	13,300
051144-81732-0	5"	Extra Hard	12,000

## 3M™ Disc Retainer Nuts



UPC	Length	Thread Size
051111-51047-6	5/16"	5/8-11 INT
051144-05622-4	3/8"	5/8-11 INT

## 3M™ Air Tool and Compressor Lubricants



UPC	Size
051141-20466-6	Quart
051141-20467-3	Gallon
051141-20451-2	4 fl. oz. (118mL)
051141-28828-4	1 fl. oz.

## 3M™ 935 Mini Mandrel



UPC	Shank Size	Overall Length	Max RPM
048011-04020-2	1/4"	2-7/8"	14,000

## 3M™ Square/Cross Pad Mandrels

UPC	Thread Size	Shank Size	Overall Length
<b>Max RPM = 24,100</b>			
051144-14307-8	8-32 EXT	1/4"	3"
051144-14308-5	1/4-20 EXT	1/4"	3"

## 3M™ Unitized Wheel Mandrels



UPC	Part No.	Overall Length	Outside Flange Diameter	Max RPM
<b>Shank Size = 1/4"</b>				
048011-04018-9	936	2-1/16"	3/4"	22,200
048011-15012-3	990	1-3/4"	1"	25,100

## 3M™ Adapters



UPC	Size
<b>3M™ Wheel Adapter Kit</b>	
051141-28419-4	1/2-20 EXT x 5/8-11 INT
051144-45038-1	5/8-11 EXT x 5/8-11 INT
<b>3M™ Spindle Extender Kit</b>	
048011-04019-6	5/8-11 EXT x 5/8-11 INT
<b>Replacement Spacers</b>	
051141-28636-5	1" OD x 5/8" ID x 3/8" thick
051141-28637-2	1" OD x 5/8" ID x 3/16" thick
<b>3M™ Match and Finish Adapter Kit</b>	
051141-27819-5	1" x 5/8-11 INT

## 3M™ Rubber Cushion Polishing Wheels



UPC	Diameter	Width	Max RPM
<b>Shank Size = 1/4"</b>			
051144-45139-5	1"	1"	18,000
051144-45129-6	2"	1"	11,000

## 3M™ Rubber Slotted Expander Wheels



UPC	Size	Density	Max RPM
051144-77717-4	1" x 1" x 1/4"	Medium	18,000
051144-77720-4	2" x 1" x 1/4"	Medium	12,000
051144-77721-1	2" x 2" x 1/4"	Medium	6,000
051144-77722-8	3" x 3" x 5/8-11 INT	Medium	6,000
051141-28349-4	3.4" x 3" x 5/8" CH	Soft	3,500
051141-28348-7	5" x 3-1/2" x 5/8" CH	Soft	3,500
051141-28718-8	5" x 3-1/2" x 1" AH	Soft	3,500

## 3M™ File Belt Sander Attachment Arms



UPC	Description
051141-28368-5	Standard Style
051141-28369-2	Thin Style
051141-28370-8	Corners Style
051141-28371-5	Thick Standard Style
051141-28372-2	Corners Style
051141-28374-6	Curved Arm
051141-28375-3	Vessel Arm
051141-28376-0	Extension — Extend arms to 24" length

The full line of 3M™ Accessories is available in the Accessories for Abrasive Products catalog.