



Right Angle Grinder Cut-Off

The Norton offering of thin, unique cut-off blades delivers a full range of sizes and thicknesses for high-demand applications like cutting and cleaning metal studs, masonry stainless steel, tubing and sheet metal.



FEATURES & BENEFITS

- Fastest cutting wheels in the market
- Will deliver a fast cut with longer life without added operator pressure
- Reinforced to tackle tough portable and fixed-base cut-off applications

SPEC CHECK

Metal

Steel, Stainless, Iron, Sheet metal

Masonry

Concrete, Brick, Cinder block, Patio stones

Asphalt

Asphalt, Green concrete

Aluminum

Aluminum, Bronze, Copper

PART #	UPC-A	SIZE	MAX RPM	WHLs/ CASE
Right Angle Cut-off Blades (Type 1) - Bulk - UPC Bar Coded				
Metal - Aluminum Oxide				
07660701616	07660701616 4	4" x .040" x 5/8"	15280	25
07660701617	07660701617 1	4-1/2" x .040" x 7/8"	13580	25
07660701618	07660701618 8	5" x .040" x 7/8"	12225	25
07660702757	07660702757 3	6" x .040" x 7/8"	10185	25
Masonry - Silicon Carbide				
07660701620	07660701620 1	4" x 1/16" x 5/8"	15280	15
07660701621	07660701621 8	4-1/2" x 1/16" x 7/8"	13580	15
07660701622	07660701622 5	5" x 1/16" x 7/8"	12225	5
Metal - Gemini Aluminum Oxide				
66243527956	66243527956 9	4" x .040" x 5/8"	15280	25
66252823602	66252823602 8	4-1/2" x .045" x 7/8"	13580	25
66252823603	66252823603 5	5" x .045" x 7/8"	12225	25
66252823604	66252823604 2	6" x .045" x 7/8"	10185	25
66243527955	66243527955 2	4" x 3/32" x 5/8"	15280	25
66252823599	66252823599 1	4-1/2" x 3/32" x 7/8"	13580	25
66252823600	66252823600 4	5" x 3/32" x 7/8"	12225	25
66252823601	66252823601 1	6" x 3/32" x 7/8"	10185	25
Metal - Aluminum Oxide				
66252843208	66252843208 6	4-1/2" x 1/16" x 7/8"	13580	25
66252843209	66252843209 3	5" x 1/16" x 7/8"	12225	25
66252843210	66252843210 9	6" x 1/16" x 7/8"	10185	25
Job Packs (Pole Packs)				
Metal - Aluminum Oxide				
07660703987	07660703987 3	4" x .040" x 5/8"	15280	5/20
07660703988	07660703988 0	4-1/2" x .040" x 7/8"	13580	5/21
Right Angle Cut-off Blades (Type 27) - Bulk - UPC Bar Coded				
Metal - Aluminum Oxide				
07660705249	07660705249 0	4" x .045" x 5/8"	15280	25
66252843604	66252843604 6	4-1/2" x .045" x 7/8"	13580	25
66252842015	66252842015 1	6" x .045" x 7/8"	10185	25
07660705251	07660705251 3	7" x 1/16" x 7/8"	8600	10
Metal - Gemini Aluminum Oxide				
66252842180	66252842180 7	4" x .045" x 5/8"	15280	25
66252842026	66252842026 8	4-1/2" x .045" x 7/8"	13580	25
66252842025	66252842025 0	4-1/2" x .045" x 5/8"-11	13580	10
66252842036	66252842036 7	5" x .045" x 7/8"	12225	25
66252841939	66252841939 2	5" x .045" x 5/8"-11	12225	10
66252842202	66252842202 6	6" x .045" x 7/8"	10185	25
66252830587	66252830587 8	6" x .045" x 5/8"-11	10185	10
66252912626	66252912626 7	7" x 1/16" x 7/8"	8600	20