

## Small Diameter Reinforced Cut-off Blades

Small diameter cut-off wheels are designed for traditional cut-off applications and feature full fiberglass reinforcing. Used on small cut-off tools for fast cut-off and slotting of all types of metal.



PART #	UPC-A	SIZE	MAX RPM	WHLs/ CASE
<b>Small Diameter Cut-off Blades (Type 1) - Handy Packs</b>				
<b>Metal - Aluminum Oxide</b>				
07660747767	07660747767 5	3" x 1/16" x 3/8"	25465	25
66252843624	66252843624 5	3" x 1/16" x 3/8"	25465	5 pack w/ mandrel
07660747769	07660747769 9	Mandrel		Accessory 5
<b>Small Diameter Cut-off Blades (Type 1) - UPC Bar Coded</b>				
<b>Metal - Aluminum Oxide</b>				
07660789451	07660789451 9	3" x .035" x 3/8"	25465	25
07660789384	07660789384 0	3" x 1/8" x 3/8"	25465	25
07660789453	07660789453 3	4" x .035" x 3/8"	19100	25
07660789387	07660789387 1	4" x 1/8" x 3/8"	19100	25
<b>Small Diameter Cut-off Blades (Type 1) - Bulk - UPC Bar Coded</b>				
<b>Metal - BlueFire Zirconia Alumina</b>				
66252843174	66252843174 4	3" x .035" x 3/8"	25465	25
66252843175	66252843175 1	3" x 1/16" x 3/8"	25465	25
66252843173	66252843173 7	4" x .035" x 3/8"	19100	25
66252843171	66252843171 3	4" x 1/16" x 3/8"	19100	25
66252843172	66252843172 0	4" x 1/8" x 3/8"	19100	25

PART #	UPC-A	SIZE	MAX RPM	WHLs/ CASE
<b>Small Diameter Cut-off Blades (Type 1) - Bulk - Non UPC</b>				
<b>Metal - Aluminum Oxide</b>				
66243411393	66243411393 2	2" x .035" x 1/4"	30560	25
66243411395	66243411395 6	2" x 1/16" x 1/4"	30560	25
66243411402	66243411402 1	2" x 1/8" x 1/4"	30560	25
66243510627	66243510627 8	3" x .035" x 1/4"	25465	25
66243510628	66243510628 5	3" x .035" x 3/8"	25465	25
66243510645	66243510645 2	3" x 1/16" x 1/4"	25465	25
66243510647	66243510647 6	3" x 1/16" x 3/8"	25465	25
66243510650	66243510650 6	3" x 1/8" x 1/4"	25465	25
66243510651	66243510651 3	3" x 1/8" x 3/8"	25465	25
66243510629	66243510629 2	4" x .035" x 1/4"	19100	25
66243510630	66243510630 8	4" x .035" x 3/8"	19100	25
66243510654	66243510654 4	4" x 1/16" x 1/4"	19100	25
66243510655	66243510655 1	4" x 1/16" x 3/8"	19100	25
66243510658	66243510658 2	4" x 1/8" x 1/4"	19100	25
66243510659	66243510659 9	4" x 1/8" x 3/8"	19100	25

## Circular Saw Reinforced Cut-off Blades

Used for deburring, cleaning, slotting and cutting of all types of metal and masonry. This includes cutting sheet metal and roof decking.



PART #	UPC-A	SIZE	MAX RPM	WHLs/ CASE
<b>Circular Saw Reinforced Cut-off Blades (Type 1) - Handy Packs</b>				
<b>Metal - Aluminum Oxide</b>				
07660789000	07660789000 9	6-1/2" x 1/8" x DM-5/8	9405	20
07660789005	07660789005 4	7" x 1/8" x DM-5/8	8730	20
07660789010	07660789010 8	8" x 1/8" x DM-5/8	7640	20
<b>Masonry - Silicon Carbide</b>				
07660789050	07660789050 4	6-1/2" x 1/8" x DM-5/8	9405	20
07660789055	07660789055 9	7" x 1/8" x DM-5/8	8730	20
07660789070	07660789070 2	8" x 1/8" x DM-5/8	7640	20

PART #	UPC-A	SIZE	MAX RPM	WHLs/ CASE
<b>Circular Saw Reinforced Cut-off Blades (Type 1) - Bulk - UPC Bar Coded</b>				
<b>Metal - Aluminum Oxide</b>				
07660789098	07660789098 6	6-1/2" x 1/8" x DM-5/8	9405	10
07660789097	07660789097 9	7" x 1/8" x DM-5/8	8730	25**
07660789096	07660789096 2	8" x 1/8" x DM-5/8	7640	10
<b>Masonry - Silicon Carbide</b>				
07660789089	07660789089 4	6-1/2" x 1/8" x DM-5/8	9405	10
07660789088	07660789088 7	7" x 1/8" x DM-5/8	8730	25**
07660789086	07660789086 3	8" x 1/8" x DM-5/8	7640	10