

# Wire Form Fan Guards - 08 Series



All wire form fan guards are produced in our ISO 9001 certified facility to assure compliance to our rigid specifications. Available for fan sizes 25mm to 254mm with a high quality nickel chrome finish as our standard. Also available in black finish & stainless steel.

08245 (25mm)	08346 (30mm)	08149 (40mm)	08148 (50mm)	08147 (60mm)	08212 (60mm)	08138 (80mm)	08132 (80mm)
08156 (80mm)	08172 (80mm)	08133 (92mm)	08134 (92mm)	08174 (92mm)	08189 (92mm)	08128 (120mm)	08129 (120mm)
08130 (120mm)	08139 (120mm)	08141 (120mm)	08146 (120mm)	08170 (120mm)	08213 (120mm)	08150 (127mm)	08125 (150mm)
08126(150mm)	08152 (150mm)	08190 (176mm)	08717 (180mm)	08718 (225mm)	08127 (254mm)	08155 (254mm)	08719 (280mm)

Part * Number	For Use With Fan Size		Rib Material Dia.		Ring Material Dia.		Mounting Hole Centers		Outside Ring Dia.		Thickness	
	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
08245	25	1	1.50	.059	1.50	.059	20.0	0.79	24.2	.953	3.00	.120
08346	30	1	1.60	.063	1.60	.063	24.0	0.94	21.8	.860	4.80	.189
08149	40	1 1/2	1.60	.063	1.60	.063	32.0	1.26	29.5	1.16	4.80	.189
08148	50	2	1.60	.063	1.60	.063	42.0	1.65	41.1	1.62	4.80	.189
08147	60	2 1/2	1.60	.063	1.60	.063	50.0	1.97	53.0	2.05	5.20	.205
08212	60	2 1/2	1.60	.063	1.60	.063	50.0	1.97	53.0	2.09	5.20	.205
08132	80	3 1/8	1.80	.071	1.60	.063	71.4	2.81	76.2	3.00	4.95	.195
08138	80	3 1/8	1.80	.071	1.60	.063	100.9	3.97	76.2	3.00	4.95	.195
08156	80	3 1/8	1.80	.071	1.80	.071	71.4	2.81	77.2	3.04	5.08	.200
08172	80	3 1/8	1.60	.063	1.60	.063	71.4	2.81	76.2	3.00	4.95	.195
08133	92	3 5/8	1.80	.071	1.60	.063	82.4	3.25	89.4	3.52	4.95	.197
08134	92	3 5/8	1.80	.071	1.60	.063	82.5	3.25	89.8	3.54	4.95	.195
08174	92	3 5/8	1.60	.063	1.60	.063	82.4	3.24	89.8	3.54	5.00	.195
08189	92	3 5/8	1.80	.071	1.60	.063	82.4	3.24	89.8	3.54	3.10	.122
08128	120	4 1/2	1.80/2.30	.071/.091	1.80	.071	104.8	4.13	115.6	4.55	5.90	.232
08129	120	4 1/2	2.30	.091	1.80	.071	104.8	4.13	115.6	4.55	3.75	.148
08130	120	4 1/2	2.30	.091	1.80	.071	104.8	4.13	115.6	4.55	5.66	.223
08139	120	4 1/2	2.30	.091	1.80	.071	104.8	4.13	115.6	4.55	5.66	.223
08141	120	4 1/2	2.00	.080	1.60	.063	104.8	4.13	117.3	4.62	5.20	.205
08146**	120	4 1/2	1.60	.063	1.60	.063	104.8	4.13	107.9	4.25	3.10	.122
08170	120	4 1/2	1.80	.071	1.80	.071	104.8	4.13	115.6	4.55	5.66	.223
08213	120	4 1/2	2.30	.091	1.80	.071	104.8	4.13	106.4	4.19	5.66	.223
08135	127	5	2.30	.091	1.80	.071	113.3	4.46	115.2	4.54	6.00	.236
08150	127	5	2.30	.091	1.80	.071	113.3	4.46	124.5	4.90	5.90	.232
08125	150	6	2.30	.091	1.80	.071	162.0	6.38	154.4	6.08	6.45	.254
08126	150	6	2.30	.091	1.80	.071	162.0	6.38	154.4	6.08	6.45	.254
08151	150	6	1.60	.063	1.60	.063	161.9	6.38	158.8	6.25	6.10	.240
08152	150	6	1.60	.063	1.60	.063	161.9	6.38	158.8	6.25	6.10	.240
08190**	176	7	2.00	.080	1.60	.063	152.6	6.00	160.9	6.33	16.31	.642
08717	180	7	2.30	.091	1.80	.071	152.2	5.99	169.6	6.68	5.50	.220
08718	225	8.9	2.30	.091	1.60/2.30	.063/.091	240.0	9.45	207.9	8.19	8.20	.320
08127	254	10	2.30	.091	2.30	.091	174.0	6.85	222.3	8.75	6.35	.250
08155	254	10	2.00	.080	2.00	.080	174.0	6.85	225.3	8.87	5.80	.228
08243-SS	254	10	1.60	.063	1.60	.063	208.0	8.19	180.8	7.12	4.00	.157
08719	280	11	2.40	.094	1.50/2.40	.059/.094	295.0	11.61	267.3	10.52	8.30	.330

\* Note: Add to part number for: Black (-02), Stainless Steel (-SS) (example: 08149-02 Black 40mm Fan Guard.)

\*\* Does not meet 1/4" max. ring spacing.

## Fan Accessories Guide - DC Fans

Fan Series	Wire Form Fan Guard	Aluminum Fan Filters	Plastic Fan Guards	Plastic Fan Filter Assemblies	QLM Vibration Sleeve
FAD1-02510	08245				
FAD1-03010	08346				
FAD1-04010	08149		09150-G	09150-F/**	
FAD1-04020	08149		09150-G	09150-F/**	
FAD1-05010	08148				
FAD1-06020	08147	06250-B, 06250-M, 06250-SS	09250-G	09250-F/**	
FAD1-06025	08147	06250-B, 06250-M, 06250-SS	09250-G	09250-F/**	
FAD1-08015	08132, 08172	06325-B, 06325-M, 06325-SS	09252-G, 09080-G, 09081-G, 09325-G	09325-F/**	
FAD1-08015 IC	08132, 08172	06325-B, 06325-M, 06325-SS	09252-G, 09080-G, 09081-G, 09325-G	09325-F/**	
FAD1-08025	08132, 08172	06325-B, 06325-M, 06325-SS	09252-G, 09080-G, 09081-G, 09325-G	09325-F/**	QLM-80-40-10, QLM-80-40-20
FAD1-08025 IC	08132, 08172	06325-B, 06325-M, 06325-SS	09252-G, 09080-G, 09081-G, 09325-G	09325-F/**	QLM-80-40-10, QLM-80-40-20
FAD1-08032	08132, 08172	06325-B, 06325-M, 06325-SS	09252-G, 09080-G, 09081-G, 09325-G	09325-F/**	QLM-80-40-10, QLM-80-40-20
FAD1-08038	08132, 08172	06325-B, 06325-M, 06325-SS	09252-G, 09080-G, 09081-G, 09325-G	09325-F/**	QLM-80-40-10, QLM-80-40-20
FAD1-09225	08134, 08174, 08189	06362-B, 06362-M, 06362-SS	09362-G, 09363-G	09362-F/**	QLM-92-40-10, QLM-92-40-20
FAD1-09225 IC	08134, 08174, 08189	06362-B, 06362-M, 06362-SS	09362-G, 09363-G	09362-F/**	QLM-92-40-10, QLM-92-40-20
FAD1-12025	08129, 08130, 08141, 08170, 08213	06450-B, 06450-M, 06450-SS	09120-G, 09121-G, 09122-G, 09123-G, 09450-G	09450-F/**	QLM-119-50-10, QLM-119-50-20
FAD1-12032	08129, 08130, 08141, 08170, 08213	06450-B, 06450-M, 06450-SS	09120-G, 09121-G, 09122-G, 09123-G, 09450-G	09450-F/**	QLM-119-50-10, QLM-119-50-20
FAD1-12038	08129, 08130, 08141, 08170, 08213	06450-B, 06450-M, 06450-SS	09120-G, 09121-G, 09122-G, 09123-G, 09450-G	09450-F/**	QLM-119-40-10, QLM-119-40-20
FAD1-12738	08135				
FDD1-17238	08125		09651-G		
FDD1-17251	08125		09651-G		
FDD1-17251 IP56M	08125		09651-G		