






REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP
C	Updated Specifications	01-10-08	DP
D	Updated Notes	11-13-08	LY



CONTROLLED

3	Soldering PIN B 0.6t Tin-Plated	1
2	Soldering PIN A 0.6t Tin-Plated	2
1	Body Insulator NYLON 21SP Color: Black	1

Dim range (mm)	Tolerance +/- (mm)	Qualtek Electronics Corp. PPC DIVISION			
		Part Number:	738W-X2/03 <div>RoHS Compliant</div>		
0-1	0.15	Description: NEMA 5-15 RECEPTACLE			
1-6	0.20				
6-18	0.30				
18-50	0.50		UNIT: mm	REV.D	
50-120	0.70		Drawn / Date	Checked / Date	Approved / Date
120-250	0.90		B. ZHANG 01-29-04	01-29-04	JJH / 01-29-04
250-500	1.20				

RATING: 15A 125V AC
MATERIAL: UL94-V0
APPROVALS: UL, cUL, CSA
PANEL THICKNESS: 0.8mm~2.0mm
MAXIMUM OPERATING TEMPERATURE: 105°C
RoHS COMPLIANT