

Plastic Fasteners Module Retainers

Part Number: SD6270UG






Replaced by SSPI-06-04

ADD TO CART

Specifications

	Type	Open / Domed
	Mandrel Material	Steel
	Body Material	Steel (AISI 1006)
	Length (L)	10.5 (mm)
	Flange Height (E)	2.2 (mm)
	Flange Diameter (H)	9.8 (mm)
	Body Diameter (D)	4.7 (mm)

Strength Data

Head Image	Riveting Thickness	Tensile Strength	Shear Strength	IFI Mandrel Breakload.
				
5	1.6 - 6.9	4890	6230	6900 - 7450