

Other Breakstem

N Rivet and BD Series

Non-structural blind breakstem rivet designed for a wide range of applications. Available in a variety of materials and combinations.



- Cost effective standard rivet
- Installed quickly and easily
- Design of the stem head ensures positive retention after installation
- Sizes from \varnothing 2.4 mm (3/32") to 6.4 mm (1/4")
- Protruding, large flange or countersunk headforms
- Materials of body/stem: aluminium/aluminium, aluminium/steel, aluminium/stainless steel, steel/steel, stainless steel/steel, stainless steel/stainless steel, monel/steel, copper/steel

Avdel® SR

Fully sealed breakstem fasteners in a wide range of materials and sizes.



- Fully sealed fastener provides a weather-proof fastener
- Good hole fill and retained stem provide strong vibration resistant joints
- Sizes from \varnothing 3.2 mm (1/8") to 6.4 mm (1/4")
- Dome head
- Materials of body/stem: aluminium/aluminium, aluminium/steel, aluminium/stainless steel, steel/steel, stainless steel/stainless steel, copper/steel

T Rivet

'Peel-type' structural breakstem rivet providing good vibration resistance and shear and tensile strength.



- High clamp-up where there is sheet separation
- Visible lock - T Rivet can withstand severe vibration without loss of the stem's plug section
- Multi-grip version available
- Sizes of \varnothing 4.8 mm (3/16") and 6.4 mm (1/4")
- Dome, large flange and countersunk headforms
- Materials of body/stem: aluminium/aluminium and aluminium/steel

Please visit our website www.avdel-global.com for technical data.