



# Plastic Fasteners Module Retainers

**Part Number: AD41-43BS**

Pop Rivet Multi-Grip Blind Rivets - Wide grip range. Ideal for use with inconsistent holes. Reduced rivet inventory

**ADD TO CART**

## Specifications

	Type	Open / Domed
	Mandrel Material	Steel
	Body Material	Aluminum
	Length (L)	0.328 (in.)
	Flange Height (E)	0.04 (in.)
	Flange Diameter (H)	0.25 (in.)
	Body Diameter (D)	0.125 (in.)

### Strength Data

Head Image



0.136

Riveting Thickness



0.039 - 0.189

Tensile Strength



220

Shear Strength



150

IFI Mandrel Breakload.



-