

Plastic Fasteners Module Retainers



Part Number: AK41-44BS

Pop Rivet Multi-Grip Blind Rivets - Wide grip range. Ideal for use with inconsistent holes. Reduced rivet inventory

ADD TO CART

Specifications



Type	Open / Countersink
Mandrel Material	Steel
Body Material	Aluminum
Length (L)	0.437 (in.)
Flange Height (E)	0.028 (in.)
Flange Diameter (H)	0.217 (in.)
Body Diameter (D)	0.125 (in.)

Strength Data

Head Image



0.136

Riveting Thickness



0.039 - 0.252

Tensile Strength



209

Shear Strength



154

IFI Mandrel Breakload.



400 - 650