

ProSet® Nose Equipment for Avdel® Breakstem Rivets

Equipements ProSet® pour rivets à rupture de tige Avdel®

ProSet® Ausrüstungen für Avdel® Dornbruchniete

Testate ProSet® per rivetti a strappo Avdel®

Equipos de colocación ProSet® - remaches de rotura de vástago Avdel®

Fastener brand	Ø mm (inch)	Material Body / Corps / Hülse / Corpo / Cuerpo	ProSet® 1600 MCS 13492 incl.: nose tips ¹⁾ PRN314, PRN414, PRN514 jaw pusher ²⁾ DPN239-144, FAN239-176	ProSet® 2500 MCS 14063 incl.: nose tips ¹⁾ PRN414, PRN514, PRN614 jaw pusher ²⁾ DPN275-027, FAN275-028	ProSet® 3400 MCS 63408 incl.: nose tips ¹⁾ PRN414, PRN514, PRN614, PRN814 jaw pusher ²⁾ DPN276-006, FAN276-064
Avinox®	3.2 (1/8")	Stainless Steel	PRN514 + DPN239-144	PRN514 + FAN275-028	
	4.0 (5/32")	Stainless Steel		PRN514 + FAN275-028	PRN514 + FAN276-064
	4.8 (3/16")	Stainless Steel		PRN614 + DPN275-027	PRN614 + DPN276-006
Avinox® XT	6.4 (1/4")	Stainless Steel			conversion kit ³⁾ : 71220-40570 + nose tip: 71233-15002
Bulbex®	4.0 (5/32")	Al. Alloy			PRN514 + FAN276-064
	4.8 (3/16")	Al. Alloy			PRN614 + DPN276-006
Klamp-Tite® non structural BAPK series	4.8 (3/16")	Al. Alloy			07381-04701 + DPN276-006
	6.4 (1/4")	Al. Alloy			07612-02001 + DPN276-006
T-Lok®	4.3	Steel		PRN514 + FAN275-028	PRN514 + FAN276-064
	4.8 (3/16")	Steel		07381-04701 + DPN275-027	07381-04701 + DPN276-006
Avdelmate®	4.8 (3/16")	any	PRN414 + DPN239-144	PRN414 + FAN275-028	PRN414 + FAN276-064
	6.4 (1/4")	any		07381-04701 + DPN275-027	07381-04701 + DPN276-006
Monobolt®	4.8 (3/16")	any			71210-16020 + DPN276-006
	6.4 (1/4")	any			71220-16021 + DPN276-006
Interlock®	4.8 (3/16")	any		PRN614 + DPN275-027	PRN614 + DPN276-006
	6.4 (1/4")	any			PRN811 + DPN276-006
Hemlok®	6.4 (1/4")	any			conversion kit ³⁾ : 71220-40560 + nose tip: 07612-02001
Q Rivet	3.2 (1/8")	any	PRN414 + DPN239-144	PRN414 + FAN275-028	
	4.0 (5/32")	any	PRN514 + DPN239-144	PRN514 + FAN275-028	PRN514 + FAN276-064
	4.8 (3/16")	any		07381-04701 + DPN275-027	07381-04701 + DPN276-006
	6.4 (1/4")	any			PRN811 + DPN276-006
Klamp-Tite® structural BAPKTR series	4.8 (3/16")	Al. Alloy			71220-16060 + DPN276-006
	6.4 (1/4")	Al. Alloy			71220-16061 + DPN276-006

1) Nose tips / nez de pose / Mundstücke / naselli / sufridera

2) Jaw pusher / poussoir de mâchoires / Klemmbackenschieber / spinda ganasce / percutor

3) Conversion kit / kit de conversion / Umbausatz / kit di conversione / kit de conversión

ProSet® Nose Equipment for Avdel® Breakstem Rivets

Equipements ProSet® pour rivets à rupture de tige Avdel®

ProSet® Ausrüstungen für Avdel® Dornbruchniete

Testate ProSet® per rivetti a strappo Avdel®

Equipos de colocación ProSet® - remaches de rotura de vástago Avdel®

Fastener brand	Ø mm (inch)	Series or / ou / oder / o Material Body / Corps / Hülse / Corpo / Cuerpo	ProSet® 1600 MCS 13492 incl.: nose tips ¹⁾ PRN314, PRN414, PRN514 jaw pusher ²⁾ DPN239-144, FAN239-176	ProSet® 2500 MCS 14063 incl.: nose tips ¹⁾ PRN414, PRN514, PRN614 jaw pusher ²⁾ DPN275-027, FAN275-028	ProSet® 3400 MCS 63408 incl.: nose tips ¹⁾ PRN414, PRN514, PRN614, PRN814 jaw pusher ²⁾ DPN276-006, FAN276-064
Standard Breakstem BD series	2.4 (3/32")	BD01, BD03	PRN314 + FAN239-176		
	3.0	BD01	PRN314 + DPN239-144		
		BD03, BD05, BD21, BD31	PRN414 + DPN239-144		
		BD11, BD13, BD24	PRN414 + DPN239-144	PRN414 + FAN275-028	
	3.2 (1/8")	BD01, BD03, BD05, BD11, BD13, BD23, BD24, BD31, BD41	PRN414 + DPN239-144	PRN414 + FAN275-028	
		BD02	PRN314 + DPN239-144		
		BD21	PRN414 + DPN239-144		
	4.0 (5/32")	BD01, BD02, BD03, BD05, BD31	PRN414 + DPN239-144	PRN414 + FAN275-028	PRN414 + FAN276-064
		BD11, BD13, BD21, BD23, BD24, BD41	PRN514 + DPN239-144	PRN514 + DPN275-027	PRN514 + DPN276-006
	4.8 (3/16")	BD01, BD02, BD03, BD05, BD31		PRN514 + DPN275-027	PRN514 + DPN276-006
		BD11, BD13, BD21, BD22, BD23, BD24, BD41		07381-04701 + DPN275-027	07381-04701 + DPN276-006
Avdel® SR	5.0	BD01, BD02, BD03, BD05		PRN514 + DPN275-027	PRN514 + DPN276-006
		BD11, BD21		07381-04701 + DPN275-027	07381-04701 + DPN276-006
	6.0	BD01, BD11, BD21			71220-60001 + DPN276-006
	6.4 (1/4")	BD01, BD11, BD21			07612-02001 + DPN276-006
Avdel® SR	3.2 (1/8")	any	PRN414 + DPN239-144	PRN414 + FAN275-028	
	4.0 (5/32")	any	PRN514 + DPN239-144	PRN514 + FAN275-028	PRN514 + FAN276-064
	4.8 (3/16")	any		PRN514 + FAN275-028	PRN514 + FAN276-064
	6.4 (1/4")	any			PRN811 + DPN276-006

1) Nose tips / nez de pose / Mundstücke / naselli / sufridera

2) Jaw pusher / poussoir de mâchoires / Klemmbackenschieber / spinda ganasce / percutor