

ProSet® XT1 - *The Lightweight*

76001-00003



Compact, lightweight and reliable pneumatic/hydraulic power tool, ideal for production line environments.

In its class the ProSet XT1 is among the highest force-to-weight ratio blind riveting tools in the industry. Innovative ergonomic design for maximum user efficiency and comfort.

The robust tool rubber base is designed to avoid damage. Latest technology lip seals maximise re-priming intervals. Piston bearing rings ensure maximum robustness and tool life.

Specifications

Weight, incl. nose equipment	1.17 kg
Weight, without nose equipment	1.07 kg
Pull force at 5.5 bar	6.5 kN
Force/Weight ratio	5.55 kN/kg
Stroke (min.)	18 mm
Cycle time (approximate)	0.4 sec
Air supply pressure (dry, filtered)	5.0 - 7.0 bar
Free air volume at 5.5 bar	1.5 l
Noise level	77.95 dB(A)

ProSet® XT2 - *The Flexible*

76002-00003



The ProSet XT2 tool sets new standards for pneumatic rivet tools. Designed specifically to set a wide range of breakstem rivets, this tool delivers 8.9 kN of pull force with an outstanding force-to-weight ratio of 7.18 kN/kg.

The robust tool rubber base is designed to avoid damage. Latest technology lip seals maximise re-priming intervals. Piston bearing rings ensure maximum robustness and tool life.

Specifications

Weight, incl. nose equipment	1.26 kg
Weight, without nose equipment	1.15 kg
Pull force at 5.5 bar	8.9 kN
Force/Weight ratio	7.06 kN/kg
Stroke (min.)	20 mm
Cycle time (approximate)	0.6 sec
Air supply pressure (dry, filtered)	5.0 - 7.0 bar
Free air volume at 5.5 bar	2.2 l
Noise level	77.1 dB(A)