



Actual

Catalog Number: GRPE-062-9-C
Product ID: 7TAG009750R0039
UPC Number: 72849410655
EAN Number: 05414363152033
Status: Active

Extruded Grommeting, Natural Polyethylene for Temperatures up to 85 Degrees Celsius (185 F), Height of 5.08mm (0.20 Inches), Width of 4.32mm (0.17 Inches), Thickness 1.14mm (0.045 Inches), Width Maximum Panel Thickness of 1.57mm (0.062 Inches), 30.48m (100 Foot) Reel

- Used to line panel edges and knockouts where the chafing of wires is a concern.
- Available in 8 stock sizes in 100-ft. lengths for panels from .040 - .250 inches thick and in a variety of stocked materials to cover a wide range of applications.
- Application Tools: SR-100

North American Specifications (UNSPSC)

UNSPSC	39131603 Grommet edging
IGCC	5393 Grommet edging
Brand Name	Catamount
Type	Grommeting
Special Features	Used to line panel edges and knockouts where the chafing of wires is a concern
Color	Natural
Length	100 Feet/30.48m
Panel Thickness	0.045 Inches/1.14mm
Material	Polyethylene

European Specifications (ETIM)

ETIM	EC002604 Cable bundle hose
Material	Plastic
Material quality	Polyethylene
Colour	Natural colour
Transparent	N

Packaging

Inner Quantity	1
Inner Dimensions (inches)	15x12x1.5
Outer Quantity	15
Outer Dimensions (inches)	18.25x12.75x13.75
Weight Uom	1.09 lbs. Each

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com