



Actual



Representative

Catalog Number: 3302-TB
Product ID: 7TAA106080R0001
UPC Number: 78621003302
EAN Number: 05414363134725
Status: Active

Sheathed Cable Fitting, Straight, Knockout Size 1/2 Inch, Two Screw Connector, Steel with Zinc Plating

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Brand Name	T&B
Sub Brand	UL E17583, CSA
Type	Non-Metallic Sheathed Cable Conduit Fittings
Special Features	Rounded Cable Grip and Smooth Bushing Protect The Cable Sheath and Wire Insulation. Since Saddle is Threaded, Screws Do Not Travel or Extend Beyond The Connector Body As It is Clamped to The Cable. An Extra Lip on The Saddle Closes The Unused Part of The Connector Opening.
Application	To Connect Non-Metallic Sheathed Cable and Flexible Cord to a Box or an Enclosure.
Standard	UL E23013, CSA 2884
Size	1/2 Inch
Connection	Straight
Material	Steel
Finish	Electro Zinc Plated
Color	Metallic
Insulation	No

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Steel
Surface protection	Zinc coated

Packaging

Inner Quantity	100
Inner Dimensions (inches)	9.5x6.5x4.5
Outer Quantity	500
Outer Dimensions (inches)	13.1x10.9x6
Weight Uom	6.25 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com