



Representative

**Catalog Number:** 5715  
**Product ID:** 7TAD012560R0005  
**UPC Number:** 78621005715  
**EAN Number:** 05414363144755  
**Status:** Active

2 Inch Neoprene Liquidtight Knockout Plug

- Made of flame retardant neoprene, these new knockout plugs meet U.L. 514 flammability test.
- Provide a raintight, dust and oil-tight reusable seal for electrical knockouts.
- NEMA 3R, 4, 6 and 13 boxes can be saved or re-used whenever a knockout is no longer used.
- No tools needed to install; just push into hole and they snap in

#### Header

3D Model Available on Website

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Knockout Plugs
Standard	UL E13938
Size	2 Inch
Material	Neoprene

#### European Specifications (ETIM)

ETIM	EC000032 Plug for cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	2 inch
Material	Plastic
Material quality	Other
Colour	Black

#### Packaging

Outer Quantity	25
Outer Dimensions (inches)	8.9x4.8x6.9
Weight Uom	9.25 lbs. per 100

#### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com