



Actual

**Catalog Number:** MPNY-750-9-D  
**Product ID:** 7TAG054850R0005  
**UPC Number:** 72849410625  
**EAN Number:** 05414363031765  
**Status:** Active

Cable Tie Mounting Base, Natural Nylon 6.6 for Temperatures up to 70 Degrees Celsius (158 F), Length of 18.79mm (0.74 Inches), Width of 18.79mm (0.74 Inches), Height of 5.08mm (0.20 Inches), Mechanical Strength 40 Newtons (9 Pounds), Hole Size #4, Synthetic Rubber Adhesive Mounting Method, 500 Pack

#### North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Catamount
Type	3/4 x 3/4 Mount
Material	Nylon/Polyamide 6.6
Color	Natural
Screw Holes	#6
Mounting	Adhesive
Operating Temperature	-40 Degree F to 185 Degree F

#### European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	18.79mm
Width	18.79mm
Height	5.08mm
Material	Plastic
Material quality	Polyamide PA
Colour	Natural colour

#### Packaging

Inner Quantity	500
Inner Dimensions (inches)	13x7x1
Outer Quantity	10000
Outer Dimensions (inches)	17.8x13x10.7
Weight Uom	1.25 lbs. per 1000

#### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-001485

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)