



Actual

**Catalog Number:** SRPE-187-9-C  
**Product ID:** 7TAG009960R0043  
**UPC Number:** 72849408386  
**EAN Number:** 05414363053255  
**Status:** Active

Spiral Wrap, Natural Polyethylene for Temperatures up to 50 Degrees Celsius (122 F), Outside Diameter of 4.75mm (0.187 Inches), Pitch of 6.10mm (0.240 Inches), Nominal Wall Thickness of 1.02mm (0.040 Inches), 30.48m Reel (100 Feet)

- Perfect for protection of bundles from .062 to 7 inch diameters.
- Install with gaps for greater flexibility or butted together for maximum abrasion resistance, insulation, and rigidity.
- Available in three material types.
- Application Tools: SR-100

## North American Specifications (UNSPSC)

UNSPSC	39131604 Spiral wrapping
IGCC	5395 Spiral wrapping
Brand Name	Catamount
Type	Spiral Wrap
Special Features	Perfect for protection of bundles from .062 to 7 inch diameters.
Color	Natural
Outside Diameter	0.187 Inches/4.75mm
Maximum Bundle Diameter	1.5 Inches/25.9mm
Minimum Bundle Diameter	0.125 Inches/3.2mm
Length	118 Feet/30.48mm
Material	Polyethylene
Wall Thickness	0.040 Inches/1.02mm

## European Specifications (ETIM)

ETIM	EC002604 Cable bundle hose
Model	Spiral hose
Nominal diameter	4.75mm
Material	Plastic
Material quality	Polyethylene
Colour	Natural colour
Transparent	N
Wall thickness	1.02mm

## Packaging

Inner Quantity	1
Outer Quantity	16
Outer Dimensions (inches)	18x13.1x13.9
Weight Uom	1.19 lbs. Each

## Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)