

Catalog Number: SS7-180
Product ID: 7TAG009430R0006
UPC Number: 78621091487
EAN Number: 05414363130055
Status: Active



Actual

Dual-Lock Mini 304 Stainless Steel Cable Tie, Temperature Rating of 538 Celsius (1000 F), Length of 165.1mm (6.5 Inches), Width of 4.5mm (0.177 Inches), Thickness of 0.381mm (0.015 Inches), Tensile Strength Rating of 445 Newtons (100 Pounds)

- Application Tools: WTA290

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5046 Stainless Steel Ties
Brand Name	Ty-Rap
Type	Mini Dual Lock
Width	0.177 Inch/4.5mm
Length	6.5 Inches/165.1mm
Bundle Diameter	1
Material	304 Stainless Steel
Color	Metallic Gray
Tensile Strength	100 Pounds/445 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.5mm
Length belt/tape/tie	165.1mm
Tie thickness	0.381mm
Min. holding force	445N
Material	Metal
Material quality	Stainless steel 304 (V2A)
Halogen free	Y
Colour	Stainless steel
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	100
Outer Quantity	1000
Weight Uom	0.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com