



Actual

Catalog Number: TC5349A-TB
Product ID: 7TCG009890R0001
UPC Number: 78621080494
EAN Number: 05414363059011
Status: Active

Re-Usable Latching Cable Clamp, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 25.0mm (0.984 Inches), Width of 25.0mm (0.984 Inches), Maximum Height of 14.5mm (0.57 Inches), Screw Mounting Method, Mounting Hole Diameter of 4.3mm (0.17 Inches), 100 Pack

- Integral top cover incorporates a unique ratchet design that is fully adjustable and releasable.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	One-Piece Mounting Clamp
Special Features	Integral top cover incorporates a unique ratchet design that is fully adjustable and releasable.
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Adhesive
Operating Temperature	-40 Degrees F to 185 Degrees F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	25mm
Width	25mm
Height	14.5mm
Type of fastening	Other
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	100
Outer Quantity	1000
Outer Dimensions (inches)	15x11.4x9.1
Weight Uom	5 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com