



Actual

**Catalog Number:** N4NY-002-0-M  
**Product ID:** 7TAG009970R0050  
**UPC Number:** 72849410546  
**EAN Number:** 05414363033721  
**Status:** Active

Plain Edge Cable Clamp, Black Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Width of 9.53mm (0.375 Inches), Thickness of 1.27mm (0.50 Inches), Hole Diameter of 4.3mm (0.170 Inches), #8 Screw Mounting with Closed Diameter of 3.2mm (0.125 Inches), Bulk Pack

- Fully radiused inside edges with size markings in inches and millimeters for easy identification.
- Plain edge cable clamps are designed to perform to NAS-1397P.

#### North American Specifications (UNSPSC)

UNSPSC	39121702 Cable clips
IGCC	5029 Nylon Cable Clips
Brand Name	Catamount
Type	Plain Edge Cable Clamps
Special Features	Fully radiused inside edges with size markings in inches and millimeters for easy identification.
Material	Nylon/Polyamide 6.6
Color	Black
Mounting	#8 Screw

#### European Specifications (ETIM)

ETIM	EC000127 Saddle
Nominal diameter	3.2mm
Model	Closed
Type of fastening	Screw hole
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
Halogen free	N
UV resistant	N
Suitable in fire resistance areas	N
Plastic sheathed	N

#### Packaging

Inner Quantity	1000
Inner Dimensions (inches)	13x7x1.5
Outer Quantity	5000
Outer Dimensions (inches)	16.25x8x7.5
Weight Uom	0.63 lbs. per 1000

#### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000389

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)