



Representative

Catalog Number: TC142X
Product ID: 7TAG009840R0007
UPC Number: 78620987440
EAN Number: 05414363500278
Status: Active

Saddle Support Mounting Base, Heat Stabilized Black Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 23.42mm (0.922 Inches), Width of 14.29mm (0.563 Inches), Height of 10.72mm (0.422 Inches), Mount with #10 Screw, Bulk Pack

- This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	Saddle Support Base
Special Features	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.
Material	Nylon/Polyamide 6.6
Color	Black
Mounting	Screw
Operating Temperature	-40 Degrees F to 185 Degrees F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	23.42mm
Width	14.29mm
Height	10.72mm
Suitable for cable tie width to	7.6mm
Type of fastening	Other
Diameter mounting hole	5.2mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Black

Packaging

Inner Quantity	500
Inner Dimensions (inches)	12x15x3
Outer Quantity	5000
Outer Dimensions (inches)	18x13x13.5
Weight Uom	1.25 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US [Available on Website](#)

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com