



Family

Catalog Number: BVID-M638GT
Product ID: 7TAA292610R0024
UPC Number: 78620995007
EAN Number: 07630030216527
Status: Active

PMAFIX Black Female Thread Adapter with Metric Threads and Universal Safety Clip, Material - Polyamide 6, Thread Size - M63x1.5, Nominal Width/ Conduit Size - 48

- Very high impact resistance
- Vibration-proof connection to PMAFLEX conduits
- Easy installation, simply push the conduit in
- High conduit pull-out strength
- Can be easily re-opened with a screwdriver
- Very good chemical properties
- Free from halogens and cadmium
- Fits both conduit profiles - Fine (T) and coarse (G)

Header

3D Model Available on Website

North American Specifications (UNSPSC)

| | |
|------------------|--|
| UNSPSC | 39121311 Electrical fittings |
| IGCC | 4441 Electrical fittings |
| Brand Name | PMA |
| Type | Adapters-Female |
| Application | For Cable Protection Systems In a Wide Range of Applications |
| Size | NW48 |
| Material | Polyamide 6 |
| Insulation Class | IP66 |
| Color | Black |
| Connection | M63 |

European Specifications (ETIM)

| | |
|---|---|
| ETIM | EC001176 Screw connection for corrugated plastic hose |
| Nominal diameter | 50mm |
| Degree of protection (IP) | IP66 |
| Model | Straight |
| Revolving thread | N |
| Construction type | External thread |
| Type of connection | Snap connection |
| Thread type | Metric |
| Thread connection size | M63 x 1.5 |
| Thread material | Polyamide |
| Thread length | 10mm |
| Total length | 65.5mm |
| Material | Polyamide |
| Material sealing | No sealing |
| Colour | Black |
| Approved in combination with protective conduit CSA | N |
| Approved in combination with protective conduit UR | Y |
| | N |

Approved in combination with protective
conduit DIN EN 61386-23

Approved in combination with protective N
conduit Lloyd's Register

Operating temperature -40 - +105°C

Packaging

| | |
|---------------------------|---------------------|
| Inner Quantity | 10 |
| Outer Quantity | 40 |
| Outer Dimensions (inches) | 15.748x11.811x7.874 |
| Weight Uom | 0.02 lbs. Each |

Documents / Support Tools

Technical Data Sheet CA Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com