



Representative



Family

Catalog Number: **ALND-M323**
Product ID: 7TAA292000R0031
UPC Number: 78620994314
EAN Number: 07630030203299
Status: Active

Smart Line Straight Black Connector with Integral Cone Seal, Material Polyamide 6, Conduit Size NW23, Thread Size - M32x1.5

- Easy push-in installation
- Easy re-opening with screwdriver
- Space savings due to compact design
- Self-extinguishing, free of halogens and cadmium
- Excellent impact strength
- Fits both conduit profiles - fine (T) and coarse (G)

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	PMA
Type	Connectors-Straight
Application	Machine Building, Installation and Construction Industries
Size	NW23
Connection	M32x1.5
Material	Polyamide 6
Color	Black

European Specifications (ETIM)

ETIM	EC001176 Screw connection for corrugated plastic hose
Nominal diameter	25mm
Degree of protection (IP)	IP66
Model	Straight
Revolving thread	N
Construction type	Internal thread
Type of connection	Snap connection
Thread type	Metric
Thread connection size	M32 x 1.5
Thread material	Polyamide
Thread length	15mm
Total length	48.5mm
Material	Polyamide
Material sealing	No sealing
Colour	Black
Approved in combination with protective conduit CSA	N
Approved in combination with protective conduit UR	N
Approved in combination with protective conduit DIN EN 61386-23	N
Approved in combination with protective conduit Lloyd's Register	N

Operating temperature -45 - +105°C

Packaging

Inner Quantity	50
Outer Quantity	250
Outer Dimensions (inches)	15.748x11.811x7.874
Weight Uom	0.03 lbs. Each

Documents / Support Tools

Video US 1 Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com