



Family

Catalog Number: **LLPFG-48A.30**
Product ID: 7TAA292030R0056
UPC Number: 78620995786
EAN Number: 07630030249433
Status: Active

Coarse Profile Medium-Wall Flexible Black Conduit, (LLPF) Material - Polyamide 6, Conduit Size NW - 48, 30 Meters

- Very good flammability characteristics
- Self-extinguishing
- Free from halogens and cadmium
- Good flexibility
- Good pressure resistance
- Good impact resistance
- Good weather resistance
- Renewable Energy

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	PMA
Type	Medium Wall Conduit
Application	Machine
Trade Size	NW48
Outside Diameter	2.15 Inch
Length	30 Meters
Flexibility	Medium Flexibility
Material	Polyamide/Nylon 6
Color	Black

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal diameter	50mm
Outer diameter	54.5mm
Inner diameter	47mm
Material	Polyamide 6
Compressive strength	175N
Operating temperature	-40 - +105°C
Fire resistance in accordance with UL94	V0
UV resistant	Y
Colour	Black
Sheathing material	Not sheathed
Bending strength	Flexible
Lengthwise slotted	N
Closable (two-part)	N
Halogen free	Y
Approved according to DIN EN 61386-23	N
Approved according to UR	N
Approved according to CSA	N
Approved according to LUL/British Standard	N
Approved according to Lloyd's Register TA	Y

Approved according to UTAC	N
Approved according to DIN 5510	N
Approved according to NF F 16-101	N

Packaging

Inner Quantity	1
Outer Quantity	4
Outer Dimensions (inches)	47.244x31.496x29.528
Weight Uom	0.07 lbs. Each

Documents / Support Tools

Video US 1	Available on Website
------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com