



Actual

Catalog Number: 204212
Product ID: 7TAI029020R0005
UPC Number: 78621086763
EAN Number: 05414363111641
Status: Active

Insulation Piercing Magnet Wire Ring Terminal, Length 1.58 Inches, Width .50 Inches, Length of Teeth .61 Inches, Width of Teeth .53 Inches, Stud Size 1/4 Inch, Wire Range #12 AWG - #4 AWG 10,380 Circular Mil Area - 52,480 Circular Mil Area, Copper Alloy, Tin Plated

- Designed to penetrate magnet wire insulation during application, eliminating the need for stripping, brazing, welding or other methods of joining magnet wire.
- For aluminum to copper, aluminum to aluminum or copper to copper magnet wire connections.

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Dragon Tooth
Type	Ring Terminals
Special Features	Designed to penetrate magnet wire insulation during application, eliminating the need for stripping, brazing, welding or other methods of joining magnet wire.
Application	For aluminum to copper, aluminum to aluminum or copper to copper magnet wire connections.
Standard	UL E9809
Material	Copper

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
AWG-range	12-4
Model	Standard version
Sleeve form	Short
Suitable for solid cores	N
Useful for stranded conductors	N
Suitable for fine strand conductors	N
Suitable for insulated varnish	Y
Suitable for round conductors	Y
Suitable for flat conductors	Y
Material	Copper
Surface protection	Tinned
Insulation	None
Voltage row	Up to 600 V
Type of connection	End connector
Oil stop/centre bar	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	500
Outer Dimensions (inches)	23.9x5.5x4
Weight Uom	2.69 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Instruction Sheet 1	ta00193-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com