



Actual

Catalog Number: TC823-TB
Product ID: 7TAG009860R0007
UPC Number: 78621082634
EAN Number: 05414363059271
Status: Active

Push-In Mounting Base, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 11.33mm (0.446 Inches), Width of 11.33mm (0.446 Inches), Height of 17.0mm (0.669 Inches), Bulk Pack

North American Specifications (UNSPSC)

UNSPSC	39121717 Cable tie mounts
IGCC	5065 Cable tie mounts
Brand Name	Ty-Rap
Type	Push Mount
Material	Nylon/Polyamide 6.6
Color	Natural
Mounting	Push Mount
Operating Temperature	-40 Degree F to 185 Degree F

European Specifications (ETIM)

ETIM	EC000449 Mounting base and -element for cable ties
Length	11.33mm
Width	11.33mm
Height	17mm
Suitable for cable tie width to	4.8mm
Type of fastening	With push fit plug
Diameter mounting hole	6.5mm
Material	Plastic
Material quality	Polyamide PA
Operating temperature	-40-+85°C
Colour	Natural colour

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	13x17x2
Outer Quantity	10000
Outer Dimensions (inches)	15.25x12.75x8.75
Weight Uom	0.13 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com