



Actual

Catalog Number: RBB217-200
Product ID: 7TAI029500R0021
UPC Number: 78621081955
EAN Number: 05414363158868
Status: Active

Expanded Vinyl Insulated Butt Splice, Length 1.13 Inches, Width .26 Inches, Maximum Insulation Diameter .200, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated, 1,000 Pack

- In butt splices, the wires are butted together and crimped at each end of the splice.
- These splices are color-coded according to wire size.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: 2RB14X

North American Specifications (UNSPSC)

UNSPSC	39121449 Wire or cable compression splice
IGCC	4669 Wire or cable compression splice
Brand Name	Sta-Kon
Type	Splice Connector
Special Features	In butt splices, the wires are butted together and crimped at each end of the splice. These splices are color-coded according to wire size.
Standard	UL E9809
Material	Copper
Finish	Electro -Tin Plated
Color	Blue
Voltage Rating	600V
Temperature Rating	105 Degrees C

European Specifications (ETIM)

ETIM	EC001059 Crimp splices for copper conductor
AWG-range	16-14
Material	Copper
Surface protection	Tinned
Insulation	PVC
Colour insulation	Blue

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	6.1x5.1x4.19
Outer Quantity	10000
Outer Dimensions (inches)	12.8x10.9x10.7
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com