



Actual

**Catalog Number:** F2026  
**Product ID:** 7TAI029790R0004  
**UPC Number:** 78621033995  
**EAN Number:** 05414363151074  
**Status:** Active

Polypropylene-Insulated Ferrule, Total Length .709 Inches/18.0mm, Pin Length .472 Inches/12mm, Pin Diameter .051 Inches/1.3mm, Base Diameter .11 Inches/2.8mm, Wire Range 18 AWG/.75mm<sup>2</sup>, Color Gray, Copper, Tin Plated

- Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
- Application Tools: T1, T3, ERG4

## North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ferrule
Special Features	Ferrules ensure reliable electrical connections when terminating conductors in screw clamp terminal blocks.
Standard	UL E489056
Wire Size	18
Material	Copper
Color	Gray

## European Specifications (ETIM)

ETIM	EC000005 Cable end sleeve
Nominal cross section	0.75mm <sup>2</sup>
Insulated	Y
Insulation material	Polypropylene
Colour	Grey
Material	Copper
Surface protection	Tinned
Reel packaging	N

## Packaging

Inner Quantity	500
Outer Quantity	5000
Outer Dimensions (inches)	7.6x5.3x4.5
Weight Uom	0.63 lbs. per 1000

## Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)