



Actual

**Catalog Number:** GRNY-085-9-C  
**Product ID:** 7TAG009750R0026  
**UPC Number:** 72849409407  
**EAN Number:** 05414363023586  
**Status:** Active

Extruded Grommeting, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Height of 5.08mm (0.20 Inches), Width of 4.32mm (0.17 Inches), Thickness 1.14mm (0.045 Inches), Width Maximum Panel Thickness of 2.15mm (0.085 Inches), 30.48m (100 Foot) Reel

- Used to line panel edges and knockouts where the chafing of wires is a concern.
- Available in 8 stock sizes in 100-ft. lengths for panels from .040 - .250 inches thick and in a variety of stocked materials to cover a wide range of applications.
- Application Tools: SR-100

#### North American Specifications (UNSPSC)

UNSPSC	39131603 Grommet edging
IGCC	5393 Grommet edging
Brand Name	Catamount
Type	Grommeting
Special Features	Used to line panel edges and knockouts where the chafing of wires is a concern
Color	Natural
Length	100 Feet/30.48m
Panel Thickness	0.085 Inches/2.15mm
Material	Nylon/Polyamide 6.6

#### European Specifications (ETIM)

ETIM	EC000879 Feed through spout
For wall thickness	2.15-2.15mm
Total length	30480mm
Model	Open
Shrink technique	N
Angle model	N
Material	Plastic
Material quality	Polyamide
Surface protection	Untreated
Halogen free	Y
Colour	Natural colour
Gastight	N
Fire resistant	Y
Watertight	N

#### Packaging

Inner Quantity	1
Inner Dimensions (inches)	15x12x2
Outer Quantity	15
Outer Dimensions (inches)	18.2x13x13.7
Weight Uom	1.28 lbs. Each

#### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**