



Actual

Catalog Number: L-4-18-9-M
Product ID: 7TAG054060R0022
UPC Number: 72849491470
EAN Number: 05414363078074
Status: Active

Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 100.08mm (3.94 Inches), Width of 2.41mm (0.095 Inches), Thickness of 1.13mm (0.045 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), Bulk Pack

- Application Tools: ERG50, QC-100, L-200, L-400-C

North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5034 Cable ties
Brand Name	Catamount
Type	Minature
Standard	UL E49405
Width	0.095 Inch/2.41mm
Length	3.94 Inches/100.08mm
Thickness	0.045 Inch/1.13mm
Bundle Diameter	0.0625 Inches/1.59mm-0.63 Inches/16mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	18 Pounds/80 Newtons

European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.41mm
Length belt/tape/tie	100.08mm
Tie thickness	1.13mm
Min. holding force	80N
Model	Internal toothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	13x17x7
Outer Quantity	25000
Outer Dimensions (inches)	17x13.6x10.5
Weight Uom	0.66 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000218

For further technical assistance, please contact us...