



Representative

Catalog Number: 54131UB
Product ID: 7TAH007890R0446
UPC Number: 78621080750
Status: Active

Copper One-Hole Lug, 90 Degree Bend Standard Barrel, Peep Hole, Max 35kV, Wire Size #8 AWG, 5/16 Inch Bolt Size, Tin Plated, Die Code 21, Die Color Code Red

North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel Copper Lug
Standard	UL E9809
Cable Size	#8 AWG
Stud Size	5/16 Inch
Number Of Holes	1
Material	Copper
Color	Red

European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	90°
Slender flange model	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

Packaging

Outer Quantity	500
Outer Dimensions (inches)	12.45x6.25x3.6
Weight Uom	1 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com