



Representative

Catalog Number: D10711
Product ID: 7TAI029620R0055
UPC Number: 78621082956
EAN Number: 05414363150046
Status: Active

Non-Insulated Tubular Ring Terminal, Length 1.20 Inches, Width .45 Inches, Bolt Hole 1/4 Inch, Wire Range 8/8AN, Copper, Tin Plated

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Application Tools: WT115A, TBM6, TBM6S, WT3185

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
Standard	UL E9809
Wire Size	8
Voltage Rating	600V
Material	Copper
Color	Metallic

Packaging

Inner Quantity	200
Inner Dimensions (inches)	3.5x3x3
Outer Quantity	2000
Outer Dimensions (inches)	16.5x7.8x3.8
Weight Uom	1.5 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000168

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com