



Representative

Catalog Number: G973
Product ID: 7TAI029610R0012
UPC Number: 78621081254
EAN Number: 05414363151746
Status: Active

Non-Insulated Tubular Ring Terminal, Length 1.59 Inches, Width .69 Inches, Bolt Hole 3/8 Inch, Wire Range 2/2AN, Copper, Tin Plated, 100 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Application Tools: WT115A, TBM6, TBM6S, WT3185

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
Standard	UL E9809
Wire Size	2
Voltage Rating	600V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
Material	Copper
Surface protection	Tinned

Packaging

Inner Quantity	100
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	1000
Outer Dimensions (inches)	23.8x10.9x3.5
Weight Uom	3 lbs. per 100

Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000219

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com