



Representative

Catalog Number: K8-10R-D
Product ID: 7TAI029110R0049
UPC Number: 78621010942
EAN Number: 05414363077350
Status: Active

Non-Insulated Large Ring Terminal for Wire Range 8 AWG Stud Size #10, Metallic

- Brazed Seam ensures barrel does not separate during crimping. Chamfered barrel entry.
- Application Tools: TBM6, TBM6S

North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Spec-Kon
Type	Ring Terminal
Special Features	Brazed Seam ensures barrel does not separate during crimping. Chamfered barrel entry.
Standard	UL E9809
Wire Size	8 AWG
Voltage Rating	600V
Material	Copper
Color	Metallic

European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N

Packaging

Inner Quantity	500
Inner Dimensions (inches)	7x5x3.25
Outer Quantity	5000
Outer Dimensions (inches)	18x11x8.2
Weight Uom	5.63 lbs. per 1000

Documents / Support Tools

Technical Data Sheet Global	wsd-000320
-----------------------------	------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com