



Representative

**Catalog Number:** K973  
**Product ID:** 7TAI029610R0020  
**UPC Number:** 78621081579  
**EAN Number:** 05414363077367  
**Status:** Active

Non-Insulated Tubular Ring Terminal, Length 2.08 Inches, Width .93 Inches, Bolt Hole 3/8 Inch, Wire Range 2/0AN-3/0, Copper, Tin Plated, 50 Pack

- These non-insulated ring terminals are made of electrolytic copper for high conductivity.
- They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
- Application Tools: TBM6, TBM6S, WT3185

## North American Specifications (UNSPSC)

UNSPSC	39121432 Electrical terminals
IGCC	4603 Electrical terminals
Brand Name	Sta-Kon
Type	Ring Terminal
Special Features	These non-insulated ring terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire).
Standard	UL E9809
Wire Size	2/0AN-3/0
Voltage Rating	600V
Material	Copper
Color	Metallic

## European Specifications (ETIM)

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	None
Reel packaging	N
Material	Copper
Surface protection	Tinned

## Packaging

Inner Quantity	50
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	250
Outer Dimensions (inches)	23.8x5.6x3.9
Weight Uom	7 lbs. per 100

## Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-000219

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)