



Actual

Catalog Number: RA250TB
Product ID: 7TAI029740R0010
UPC Number: 78621082999
EAN Number: 05414363157670
Status: Active

Nylon Insulated Female Disconnect, Length .91 Inches, Width .29 Inches, Maximum Insulation .136, Tab Size .250x.032, Wire Range #22-#18, Color Red, Copper, Tin Plated, 1,000 Pack

- Unique construction of the female disconnect offers long-term dependability.
- Brazed seam serrated barrel provides maximum tensile strength.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RA18250F

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.
Standard	UL E66716
Material	Brass
Finish	Electro -Tin Plated
Color	Red
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Red
Material insulation	PA
Material	Copper

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	10000
Outer Dimensions (inches)	16.1x9.6x6.9
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com