



Actual

Catalog Number: RB257
Product ID: 7TAI029730R0003
UPC Number: 78621081817
EAN Number: 05414363158561
Status: Active

Vinyl Insulated Female Disconnect, Length .96 Inches, Width .29 Inches, Maximum Insulation .170, Tab Size .250x.032, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated, 1,000 Pack

- Unique construction of the female disconnect offers long-term dependability.
- Brazed seam serrated barrel provides maximum tensile strength.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: 14RB250F

North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Unique construction of the female disconnect offers long-term dependability. Brazed seam serrated barrel provides maximum tensile strength.
Standard	UL E66716
Material	Brass
Finish	Electro -Tin Plated
Color	Blue
Insulation	Vinyl

European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Blue
Material insulation	PVC
Material	Copper

Packaging

Inner Quantity	1000
Inner Dimensions (inches)	6.1x4.6x3.1
Outer Quantity	10000
Outer Dimensions (inches)	16x9.8x6.8
Weight Uom	3.13 lbs. per 1000

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com