



Actual

**Catalog Number:** RBD1823  
**Product ID:** 7TAI029750R0033  
**UPC Number:** 78621081693  
**EAN Number:** 05414363158912  
**Status:** Active

Nylon Insulated Female Disconnect, Length .83 Inches, Width .23 Inches, Maximum Insulation .163, Tab Size .187x.020, Wire Range #16-#14 AWG, Color Blue, Copper, Tin Plated, 1,000 Pack

- Quick, reliable method of connection to terminal blocks and boards without the use of tools.
- Unique construction of the female disconnect offers long-term dependability.
- Application Tools: WT145C, WT2000, WT112M, ERG4001
- Alternate Package Qty: RBD14182

## North American Specifications (UNSPSC)

UNSPSC	39121447 Wire terminal disconnect
IGCC	4667 Wire terminal disconnect
Brand Name	Sta-Kon
Type	Disconnects
Special Features	Quick, reliable method of connection to terminal blocks and boards without the use of tools. Unique construction of the female disconnect offers long-term dependability.
Standard	UL E66716
Material	Brass
Finish	Electro -Tin Plated
Color	Blue
Insulation	Nylon

## European Specifications (ETIM)

ETIM	EC000516 Round or flat plug/receptacle
Insulation	Partially Insulated
Colour insulation	Blue
Material insulation	PA
Material	Copper

## Packaging

Inner Quantity	1000
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	5000
Outer Dimensions (inches)	10.5x9.1x7.2
Weight Uom	3.13 lbs. per 1000

## Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)