



Actual

Catalog Number: 330B
Product ID: 7TBA008930R0012
UPC Number: 06739600912
Status: Active

Marrette #330. Rated 105 degree C - 300 Volts. Wire range: 22-14. Blue. Box of 100.

- The only wire connector to offer a non-winged, variable-volume live-action spring in the connector.
- Accommodates a broader range of wire connection combinations.
- Coated with 100% pure copper, which reduces the corrosion common to tin and zinc-coated products.
- Features_3
- Only red non-winged connector that is U.L. listed for a pair of #8 AWG wires.

North American Specifications (UNSPSC)

UNSPSC	39121445 Twist on wire connector
IGCC	4665 Twist on wire connector
Brand Name	Marrette
Type	Wire Connectors-Non-Winged
Special Features	The only wire connector to offer a non-winged, variable-volume live-action spring in the connector.
Standard	UL E9809
Size	22-14
Color	Blue
Voltage Rating	300V
Temperature Rating	105 Degrees Celcius
Wire Type	Copper Only

Packaging

Outer Quantity	10
Outer Dimensions (inches)	7.25x6.06x7.38
Weight Uom	218.75 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com