



Actual

Catalog Number: LN-ISO25-G
Product ID: 7TAD105080R0044
UPC Number: 78621021178
EAN Number: 05415022204148
Status: Active

Locknut, 25mm ISO/Metric Thread, Nylon, Gray

- For use with non-metallic cable glands

North American Specifications (UNSPSC)

UNSPSC	31161716 Locknuts
IGCC	2849 Locknuts
Brand Name	T&B
Type	Locknut for Liquidtight Connector
Material of Construction	Nylon
Thread Size	25
Thread Type	ISO/Metric
Color	Gray

European Specifications (ETIM)

ETIM	EC000940 Locknut for cable screw gland
Thread type	Metric
Nominal thread size metric/PG	25
Material	Plastic
Material quality	Polyamide (PA)
Colour	Light grey

Packaging

Inner Quantity	10
Inner Dimensions (inches)	4.12x4.12x3.12
Outer Quantity	50
Outer Dimensions (inches)	7.75x4.25x5.5
Weight Uom	7.5 lbs. per 1000

Documents / Support Tools

Technical Data Sheet CA	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com