

4-Conductor, Chassis-Mount Terminal Strips

4- and 5-Pole, 4 mm²

862 Series

PUSH-IN CAGE CLAMP®

1

35

1

	0.5 ... 4 mm ² ① 500 V/6 kV/3 I _N 32 A	4 x AWG 20 ... 12 300 V, 20 A ② 300 V, 20 A ③	0.5 ... 4 mm ² ① 500 V/6 kV/3 I _N 32 A	4 x AWG 20 ... 12 300 V, 20 A ② 300 V, 20 A ③
	10 ... 11 mm / 0.41 in.	② Approvals	10 ... 11 mm / 0.41 in.	② Approvals

① Conductor sizes: 0.25 ... 4 mm² "s + f-st";
Push-in conductor sizes: 0.75 ... 4 mm² "s" and 0.75 ... 2.5 mm² "insulated ferrule, 12 mm"



Available in black and white.

4-pole

5-pole

	without Ground contact	with Ground contact (PE contact)	Item No. black	Item No. white	Pack. Unit	Item No. black	Item No. white	Pack. Unit
For screw and nut 3 mm Ø or for self-tapping screw 2.9 mm Ø from top								
plain			● 862-0504	○ 862-0604	200			
⊕-N-L1-L2			● 862-1504	○ 862-1604	200			
N-⊕-L1-L2			● 862-2504	○ 862-2604	200			
N-⊕-L1-L2			● 862-8504	○ 862-8604	200			
⊕-N-L1-L2			● 862-9504	○ 862-9604	200			
1 snap-in foot per pole								
plain			● 862-0534	○ 862-0634	200			
⊕-N-L1-L2			● 862-1534	○ 862-1634	200			
N-⊕-L1-L2			● 862-2534	○ 862-2634	200			
N-⊕-L1-L2			● 862-8534	○ 862-8634	200			
⊕-N-L1-L2			● 862-9534	○ 862-9634	200			
Snap-in foot at pos. 1+4								
plain			● 862-0594	○ 862-0694	200			
⊕-N-L1-L2			● 862-1594	○ 862-1694	200			
N-⊕-L1-L2			● 862-2594	○ 862-2694	200			
N-⊕-L1-L2			● 862-8594	○ 862-8694	200			
⊕-N-L1-L2			● 862-9594	○ 862-9694	200			
For screw and nut 3 mm Ø or for self-tapping screw 2.9 mm Ø from top								
plain						● 862-0505	○ 862-0605	200
⊕-N-L1-L2-L3						● 862-1505	○ 862-1605	200
L3-N-⊕-L1-L2						● 862-2505	○ 862-2605	200
L3-N-⊕-L1-L2						● 862-8505	○ 862-8605	200
⊕-N-L1-L2-L3						● 862-9505	○ 862-9605	200
1 snap-in foot per pole								
plain						● 862-0525	○ 862-0625	200
⊕-N-L1-L2-L3						● 862-1525	○ 862-1625	200
L3-N-⊕-L1-L2						● 862-2525	○ 862-2625	200
L3-N-⊕-L1-L2						● 862-8525	○ 862-8625	200
⊕-N-L1-L2-L3						● 862-9525	○ 862-9625	200
Snap-in foot at pos. 1+3+5								
plain						● 862-0515	○ 862-0615	200
⊕-N-L1-L2-L3						● 862-1515	○ 862-1615	200
L3-N-⊕-L1-L2						● 862-2515	○ 862-2615	200
L3-N-⊕-L1-L2						● 862-8515	○ 862-8615	200
⊕-N-L1-L2-L3						● 862-9515	○ 862-9615	200

862 Series Accessories

Comb-style jumper bar, simply push into conductor entry hole I _N 32 A 862-482 5	Test plug, with 500 mm cable, 2 mm Ø red 210-136 50	Test plug, with 500 mm cable, 2.3 mm Ø yellow 210-137 50
Operating tool with partially insulated shaft, type 2, (3.5 x 0.5) mm blade 210-720 1	Suitable for Ex e II applications 440 V, 28 A	Marking strip, plain, 7.5 mm wide, 50m roll white 709-178 1

For technical explanations and abbreviations, see technical section.

