

PRECISION CAPTIVE SCREWS

THREAD	STYLE	MATERIAL
#4-40 TO 10-32 UNC-2A	SLOTTED HEAD	303 STAINLESS STEEL

SLOTTED HEAD STOCK NO.	L	M	H	E	D	THREAD UN-2A
Z12-1	.281	.187	1/8	.072	1/4	#4-40
Z12-2	.343	.187	1/8	.072	1/4	#4-40
Z12-3	.312	.218	1/8	.086	9/32	#6-32
Z12-4	.375	.218	1/8	.086	9/32	#6-32
Z12-5	.437	.218	1/8	.086	9/32	#6-32
Z12-6	.406	.250	5/32	.114	5/16	#8-32
Z12-7	.468	.250	5/32	.114	5/16	#8-32
Z12-8	.531	.250	5/32	.114	5/16	#8-32
Z12-9	.531	.312	3/16	.136	3/8	#10-32
Z12-10	.593	.312	3/16	.136	3/8	#10-32

THREAD	STYLE	MATERIAL
#4-40 TO 10-32 UNC-2A	HEX SOCKET HEAD	303 STAINLESS STEEL

HEX SOCKET HEAD STOCK NO.	L	M	H	E	D	THREAD UN-2A	W
Z12-1-H	.281	.187	1/8	.072	1/4	#4-40	5/64
Z12-2-H	.343	.187	1/8	.072	1/4	#4-40	5/64
Z12-3-H	.312	.218	1/8	.086	9/32	#6-32	5/64
Z12-4-H	.375	.218	1/8	.086	9/32	#6-32	5/64
Z12-5-H	.437	.218	1/8	.086	9/32	#6-32	5/64
Z12-6-H	.406	.250	5/32	.114	5/16	#8-32	3/32
Z12-7-H	.468	.250	5/32	.114	5/16	#8-32	3/32
Z12-8-H	.531	.250	5/32	.114	5/16	#8-32	3/32
Z12-9-H	.531	.312	3/16	.136	3/8	#10-32	1/8
Z12-10-H	.593	.312	3/16	.136	3/8	#10-32	1/8

See index for hex wrenches.

THREAD	STYLE	MATERIAL
#4-40 TO 10-32 UNC-2A	KNURLED HEAD	303 STAINLESS STEEL

KNURLED HEAD STOCK NO.	L	M	H	E	D	THREAD UN-2A
Z12-1-K	.281	.187	1/8	.072	1/4	#4-40
Z12-2-K	.343	.187	1/8	.072	1/4	#4-40
Z12-3-K	.312	.218	1/8	.086	9/32	#6-32
Z12-4-K	.375	.218	1/8	.086	9/32	#6-32
Z12-5-K	.437	.218	1/8	.086	9/32	#6-32
Z12-6-K	.406	.250	5/32	.114	5/16	#8-32
Z12-7-K	.468	.250	5/32	.114	5/16	#8-32
Z12-8-K	.531	.250	5/32	.114	5/16	#8-32
Z12-9-K	.531	.312	3/16	.136	3/8	#10-32
Z12-10-K	.593	.312	3/16	.136	3/8	#10-32

